



#### NOTES:

1. Material : Stainless Steel
2. Finish :
3. ASME Y14.5M - 2009
4. All Drawing Dimensions are in Inches [mm]
5. Unless otherwise specified; Edge Breaks, Radii or Countersinks 0.005-0.015
6. Threads are Supplied Cut or Rolled at RAF's Option Unless Noted on Order.
7. Threads are to Commercial 2A and 2B Standards per Handbook H-28 (Part 1)



95 Silvermine Rd., Seymour CT 06483  
Tel: 203-888-2133, Fax: 203-888-9860

This Drawing is the Property of RAF.  
It contains confidential, proprietary  
information that is RAF property. Do  
not disclose to or duplicate for others  
except as authorized by RAF.

**TOLERANCES**  
ALL DIMENSIONS ARE INCHES  
(UNLESS OTHERWISE SPECIFIED)  
**METALLIC**  
LENGTHS  $\leq$  6 INCHES  $\pm$  0.005  
LENGTH  $>$  6 INCHES  $\pm$  0.010  
DIAMETERS:  $\pm$  0.005  
**NON-METALLIC**  
LENGTH:  $\pm$  0.010 DIAMETERS:  $\pm$  0.010  
**INTERNAL THREADS:**  
MINIMUM THREAD DEPTH

COMPONENT

PANEL SCREW

1003-125-SS

PANEL SCREW RETAINER  
STYLE A

SCALE

4.00

SHEET

1 of 1

REV	CHANGE	DATE	DRN	CHK
	Drawn	03/06/17	SJ	T

#### TOLERANCE DETAILS

1	A	$\pm 0.004$ [ $\pm 0.01$ ]
2	B	$\pm 0.002$ [ $\pm 0.05$ ]
3	C	$+ 0.004$ [ $+ 0.10$ ] $- 0.001$ [ $- 0.02$ ]
4	F	$\pm 0.005$ [ $\pm 0.12$ ]
5	G	$\pm 0.005$ [ $\pm 0.12$ ]
6	H	$\pm 0.010$ [ $\pm 0.25$ ]
7	J	$\pm 0.005$ [ $\pm 0.12$ ]

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RAF Electronic Hardware:](#)

[1003-125-ss](#)