



NOTES:

1. Material: Corrosion resistant steel (CRES) per ASTM A582/A582M, type 303 (UN S30330) or 303SE (UNS S30323) or XM-1 (UMS S20300), condition A
2. Finish: Passivate per AMS2700, Method 1, Class 4
3. All Drawing Dimensions are in Inches [mm]
4. Unless otherwise specified, Edge Breaks, Radii or Countersinks 0.005-0.015
5. All features in accordance with NAS1831



MW Industries

95 Silvermine Rd., Seymour CT 06483
Tel: 203-888-2133, Fax: 203-888-9860

This Drawing is the Property of MW Industries. It contains confidential, proprietary information that is MW Industries property. Do not disclose to or duplicate for others except as authorized by MW Industries.

TOLERANCES
ALL DIMENSIONS ARE INCHES
(UNLESS OTHERWISE SPECIFIED)
METALLIC
LENGTHS < 6 INCHES ± 0.005
LENGTH > 6 INCHES ± 0.010
DIAMETERS: ± 0.005
NON-METALLIC
LENGTH: ± 0.010 DIAMETERS: ± 0.010
INTERNAL THREADS:
MINIMUM THREAD DEPTH

COMPONENT		FEMALE FEMALE STANDOFF	
NAS1831C6E64	3/8 Female Female Standoff	SCALE	REV
		2.81	04
		SHEET	
		1 of 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RAF Electronic Hardware:](#)

[NAS1831C6E64](#)