

ICP622540PMT

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V

With Safety Circuit, **IEC62133 certified**

Specifications

Renata Type	ICP622540
IEC Designation	ICP072642
Part Number	100651
Contact Method	Wire AWG 26
Safety Circuit	Yes with NTC

Nominal Voltage	3.7 V
Nominal Capacity	600 mAh
Minimum Capacity	550 mAh (0.2C cut off 3.0 V at 20°C)

Internal Impedance	< 220 mΩ / 30% SOC
--------------------	--------------------

Thickness (t)	Max 6.5 mm
Length (l)	Max 42.5 mm
Width (w)	Max 25.7 mm
Weight	~ 11 g

Charging Characteristic

	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 300 mA
Max. Charging Current	1.0 C CC – 600 mA
Temperature at Charging	0 °C 45 °C


Discharge Characteristic

Cut off Voltage	3.0 V
Max Discharge Current	2.0 C – 1200 mA (for non continues discharge) 1.0 C – 600 mA (for continues discharge)
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature	> 80% of minimum capacity after 500 cycles (0.5 C charge, 0.5 C discharge)
--------------------------------	--

Storage Temperature	-20 °C ... 45 °C (0 °C ... 30 °C recommended in case of storage for more than 3 months)
---------------------	---

Dimensions



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative. For safety related information please consult the ASDS document related to that product or product family. The Products of Renata SA are neither designed nor authorized for use in certain areas of application of environment. For further details we refer to our webpage www.renata.com/downloads/restriction_of_use

Rev. ICP622540 V03 08/2019

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Renata:

[ICP622540PMT](#) [ICP622540PMT-01](#)