


SMLV36 series



Actual size

3528(1411)

3.5×2.8mm(t=0.6mm)

Features


- High heat radiation, high efficiency white LEDs
- Low height made possible by flat frame structure

 Color Type WB


Specifications

Part No.	Chip Structure	Emitting Color	Absolute Maximum Ratings (Ta=25°C)					Electrical and Optical Characteristics (Ta=25°C)												
			Power Dissipation Pd(mW)	Forward Current If(mA)	Peak Forward Current Ifp(mA)	Operating Temperature Topr(°C)	Storage Temperature Tstg(°C)	Forward Voltage Vf		Chromaticity Coordinates		Luminous Intensity Iv			Luminous Flux Φv					
									Typ.(V)	If(mA)	(x, y)	If(mA)	Min. (mcd)	Typ. (mcd)	If(mA)	Typ. (lm)	If(mA)			
☐ SMLV36WBFAW	InGaN	High Color Rend. (5000K)	420	105	400	-40 to +85	-40 to +100	3.4	90	(0.36,0.36)	90	4.8	7.0	90	(25)	90				
☐ SMLV36WBFBW		High Color Rend. (3000K)															(20)			
☐ SMLV36WBFCW		White																5.8	8.5	(30)
☐ SMLV36WBFDW																				


Dimensions



Recommended Solder Pattern




Viewing Angle




Electrical Characteristics Curves


Forward Current-Forward Voltage




Luminous Intensity-Atmosphere Temperature



Luminous Intensity-Forward Current



Derating


☐ SMLV36WBFAW
☐ SMLV36WBFBW
☐ SMLV36WBFCW
☐ SMLV36WBFDW

☐ SMLV36WBFAW
☐ SMLV36WBFBW
☐ SMLV36WBFCW
☐ SMLV36WBFDW

☐ SMLV36WBFAW
☐ SMLV36WBFBW
☐ SMLV36WBFCW
☐ SMLV36WBFDW

☐ SMLV36WBFAW
☐ SMLV36WBFBW
☐ SMLV36WBFCW
☐ SMLV36WBFDW


Rank Reference of Brightness

White (WB)

Package type	Package size (mm)	Height (mm)	Luminous intensity I _v (mA)																				
				C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	U			
Chip LEDs with Reflector	3528	0.6	90	2.2 to 2.8	2.8 to 3.3	3.3 to 4.0	4.0 to 4.8	4.8 to 5.8	5.8 to 7.0	7.0 to 8.5	8.5 to 10.2	10.2 to 12.3	12.3 to 14.8	14.8 to 19	19 to 21.8	21.8 to 24.5	24.5 to 27.2	27.2 to 29.3	29.3 to 32.6	32.6 to 35.4			
								SMLV36WBFAW															
								SMLV36WBFBW															
								SMLV36WBFCW															
								SMLV36WBFDW															

※Brightness on specification sheet include tolerance of within ± 10%.

Chromaticity Diagram



Part No. Construction

S

M

L

Series name

V

3

6

Package name

W

B

F

A

W

Chip Type

Emitting Color

WB

White

Chromaticity sort *2

Rank sign (Chromaticity Rank) *1

1

2

K

Resin Color

Taping Specifications

Rank sign (Brightness Rank) *1

W

MilkyWhite

1

Cathode at sprocket hole side

*1 Concerning the Brightness rank

- Please refer to the rank chart above for luminous intensity classification.
- Please refer to the Specification sheet for color classification.
- Part name is individual for each rank.
- When shipped as sample, the part name will be a representative part name.

General products are free of ranks. Please contact sales if rank appointment is needed.

*2: Please refer to Chromaticity diagram.

Packing Specification

ROHM LED products are being shipped with desiccant (silica gel) concluded in moisture-proof bags.
Pasting the moisture sensitive label on the outer surface of the moisture-proof bags or enclosing the humidity indication card inside the bag is available upon request.
Please contact the nearest sales office or distributor if necessary.

Notes

No copying or reproduction of this document, in part or in whole, is permitted without the consent of ROHM Co.,Ltd.

The content specified herein is subject to change for improvement without notice.

The content specified herein is for the purpose of introducing ROHM's products (hereinafter "Products"). If you wish to use any such Product, please be sure to refer to the specifications, which can be obtained from ROHM upon request.

Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

Great care was taken in ensuring the accuracy of the information specified in this document. However, should you incur any damage arising from any inaccuracy or misprint of such information, ROHM shall bear no responsibility for such damage.

The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM and other parties. ROHM shall bear no responsibility whatsoever for any dispute arising from the use of such technical information.

The Products specified in this document are intended to be used with general-use electronic equipment or devices (such as audio visual equipment, office-automation equipment, communication devices, electronic appliances and amusement devices).

The Products specified in this document are not designed to be radiation tolerant.

While ROHM always makes efforts to enhance the quality and reliability of its Products, a Product may fail or malfunction for a variety of reasons.

Please be sure to implement in your equipment using the Products safety measures to guard against the possibility of physical injury, fire or any other damage caused in the event of the failure of any Product, such as derating, redundancy, fire control and fail-safe designs. ROHM shall bear no responsibility whatsoever for your use of any Product outside of the prescribed scope or not in accordance with the instruction manual.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). ROHM shall bear no responsibility in any way for use of any of the Products for the above special purposes. If a Product is intended to be used for any such special purpose, please contact a ROHM sales representative before purchasing.

If you intend to export or ship overseas any Product or technology specified herein that may be controlled under the Foreign Exchange and the Foreign Trade Law, you will be required to obtain a license or permit under the Law.



Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

<http://www.rohm.com/contact/>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ROHM Semiconductor:

[SMLV36WBFAW1](#) [SMLV36WBFCW1](#) [SMLV36WBFDW1](#) [SMLV36WBFBW1](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ROHM Semiconductor:](#)

[SMLV36WBFCW1](#)