

Switching Regulator Series

Step-Down DC/DC Converter BD9A300MUV Evaluation Board

BD9A300MUV-EVK-001

Description

BD9A300MUV-EVK-001 Evaluation board delivers an output 1.8 volts from an input 2.7 to 5.5 volts using BD9A300MUV, a synchronous rectification step-down DC/DC converter integrated circuit, with output current rating of maximum 3A. It offers high efficiency in all load ranges by equipping the efficiency improvement function in light-load. The output voltage can be set by changing the external parts of circuit and the loop-response characteristics also can be adjusted by the phase compensation circuit.

Performance specification (These are representative values, and it is not a guaranteed against the characteristics.)

Parameter	Min	Тур	Max	Units	Conditions
Input Voltage Range	2.7		5.5	V	
Output Voltage		1.8		V	R1=30kΩ, R2=24kΩ
Output Voltage Setting Range	0.8		V _{IN} ×0.7	V	
Output Current Range	0		3.0	А	
Loop Band Width		89.1		kHz	
Phase Margin		54.1		degrees	
Input Ripple Voltage		140		mVpp	I _O = 3.0A
Output Ripple Voltage		40		mVpp	I _O = 3.0A
Output Rising Time		5		ms	
Operating Frequency		1.0		MHz	
Maximum Efficiency		91.8		%	I _O = 0.7A

V_{IN} = 5.0V, V_{OUT} = 1.8V, Unless otherwise specified.

Operation Procedures

- 1. Necessary equipments
 - (1) DC power-supply of 2.7V to 5.5V/3A
 - (2) Maximum 3A load
 - (3) DC voltmeter

2. Connecting the equipments

- (1) DC power-supply presets to 5.0V and then the power output turns off.
- (2) The max. load should be set at 3A and over it will be disabled.
- (3) Check Jumper pin of SW1 is short, between intermediate-terminal and OFF-side terminal.
- (4) Connect positive-terminal of power-supply to VIN+terminal and negative-terminal to GND-terminal with a pair of wires.
- (5) Connect load's positive-terminal to VOUT+terminal and negative-terminal to GND-terminal with a pair of wires.
- (6) Connect positive-terminal of DC voltmeter 1 to TP1 and negative-terminal to TP2 for input-voltage measurement.
- (7) Connect positive-terminal of DC voltmeter 2 to TP3 and negative-terminal to TP4 for output-voltage measurement.
- (8) DC power-supply output is turned ON.
- (9) IC is enable (EN) by shorting Jumper-pin of SW1 between intermediate-terminal and ON-side terminal.
- (10) Check DC voltmeter 2 displays 1.8V.
- (11) The load is enabled.
- (12) Check at DC voltmeter 1 whether the voltage-drop (loss) is not caused by the wire's resistance.



Figure 1. Connection Diagram

Enable-Pin

To minimize current consumption during standby-mode and normal operation, Enable-mode can be switched by controlling EN pin(15pin) of the IC. Standby-mode is enabled by shorting Jumper-pin of SW1 between intermediate-terminal and OFF-side terminal and normal-mode operation by shorting between intermediate-terminal and ON-side terminal. It also can be swithed between standby-mode and normal-mode operation by removing Jumper-pin and controlling the voltage between EN and GND-terminal. Standby-mode is enabled when the voltage of EN is under 0.5V and normal-mode

voltage between EN and GND-terminal. Standby-mode is enabled when the voltage of EN is under 0.5V, and normal-mode operation when it is over 2.0V.

Q

Q GND

VOUT

Cricuit Diagram

 V_{IN} = 2.7V to 5.5V, V_{OUT} = 1.8V U1 BD9A300MUV BOOT 13 PGD O **₹**R7 14 PGD TP3 L1 R4 C7 Q J2 C4 C5 C6 TP1 SW 12 16 AVIN J1 C3 C2 C1 SW 11 1 PVIN **O** TP5 SW 10 0 2 PVIN GND O **O** TP7 SS 9 TP4 O 3 PGND C9 TP2 SW1 4 PGND R3 ITH 7 15 EN OFF С ₹^{R5} C8 17 EPAD 8 MODE R1 R6 5 AGND FB 6 6 C10 **≶**R2 TP6

Figure 2. BD9A300MUV-EVK-001 Circuit Diagram

Bill of Materials

Count	Reference Designator	Туре	Value	Description	Manufacturer Part Number	Manufacturer	Configuration (mm)
2	C1, C7	Ceramic Capacitor	0.1µF	50V, B, ±10%	GRM188B31H104KA92D	MURATA	1608
1	C2	Ceramic Capacitor	10µF	16V, B, ±10%	GRM31CB31C106KA88L	MURATA	3216
0	C3	Ceramic Capacitor	-	Notinstalled	-	-	3216
2	C4, C5	Ceramic Capacitor	22µF	6.3V, B, ±20%	GRM21BB30J226ME38L	MURATA	2012
0	C6	Ceramic Capacitor	-	Notinstalled	-	-	2012
1	C8	Ceramic Capacitor	3300pF	50V, B, ±10%	GRM188B11H332KA01D	MURATA	1608
1	C9	Ceramic Capacitor	0.01µF	50V, B, ±10%	GRM188B11H103KA01D	MURATA	1608
0	C10	Ceramic Capacitor	-	Notinstalled	-	-	1608
1	L1	Inductor	1.5µH	±30%, DCR=14.3mΩmax, 7.3A	CLF7045T-1R5N	TDK	7269
1	R1	Resistor	30kΩ	1/10W, 50V, ±1%	MCR03ERPF3002	ROHM	1608
1	R2	Resistor	24kΩ	1/10W, 50V, ±1%	MCR03ERPF2402	ROHM	1608
1	R3	Resistor	9.1kΩ	1/10W, 50V, ±1%	MCR03ERPF9101	ROHM	1608
1	R4	Resistor	10kΩ	1/10W, 50V, ±1%	MCR03ERPF1002	ROHM	1608
2	R5, R7	Resistor	0Ω	Jumper	MCR03ERPJ000	ROHM	1608
0	R6	Resistor	-	Notinstalled	-	-	1608
1	SW1	Pin header	-	2.54mm × 3 contacts	PH-1x03SG	USECONN	-
1	U1	IC	-	Buck DC/DC Converter	BD9A300MUV	ROHM	VQFN016V3030
2	J1, J2	Terminal Block	-	2 contacts, 15A, 14 to 22AWG	TB111-2-2-U-1-1	Alphaplus Connectors & Cables	-
1	-	Jumper	-	Jumper pin for SW1	MJ254-6BK	USECONN	-

Layout



Figure 3. Top Silk Screen (Top view)



Figure 4. Top Silk Screen and Layout (Top view)



Figure 5. Top Side Layout (Top view)



Figure 6. L2 Layout (Top view)



Figure 7. L3 Layout (Top view)



Figure 8. Bottom Side Layout (Top view)



Figure 9. Efficiency vs Load Current

Figure 10. Line Regulation



Figure 11. Load Regulation



Figure 12. Load Transient Characteristics



Figure 13. Loop Response V_{IN} = 3.3V, V_O = 1.8V, I_O = 1.0A



Figure 14. Loop Response V_{IN} = 5.0V, V_O = 1.8V, I_O = 1.0A





Figure 18. Output Voltage Ripple Wave V_{IN} = 5.0V, V_O = 1.8V



Notes						
1)	The information contained herein is subject to change without notice.					
2)	Before you use our Products, please contact our sales representative and verify the latest specifica- tions :					
3)	Although ROHM is continuously working to improve product reliability and quality, semicon- ductors can break down and malfunction due to various factors. Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.					
4)	Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.					
5)	The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.					
6)	The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communi- cation, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.					
7)	The Products specified in this document are not designed to be radiation tolerant.					
8)	For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.					
9)	Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.					
10)	ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.					
11)	ROHM has used reasonable care to ensur the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.					
12)	Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.					
13)	When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.					
14)	This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.					



Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ROHM Semiconductor: BD9A300MUV-EVK-001