


LA-401 D / N series is developed because of the demand for small single digit LED Numeric Display. Materials of emission are GaAsP on GaP, AlGaInP and GaP. This is the height of a letter 10.16mm, single digit LED Numeric Display that is packed by EPOXY resin.


### ●Features

- 1) The height of a letter is 10.16mm.
- 2) Dimension is 9.6×13.0×7.0mm.
- 3) The package of surface color is black. Color of segment is colored in emitting color.
- 4) Each color has anode common and cathode common respectively.

### ●Dimensions (Unit : mm)





### ●Pin assignments



| Pin No. | Function    |
|---------|-------------|
| 1       | Common      |
| 2       | Segment "f" |
| 3       | Segment "g" |
| 4       | Segment "e" |
| 5       | Segment "d" |
| 6       | Common      |
| 7       | D.P         |
| 8       | Segment "c" |
| 9       | Segment "b" |
| 10      | Segment "a" |

### ●Internal circuit schematic



### ●Selection guide

| Emitting color | Red      | Red (High brightness) | Orange (High brightness) | Yellow (High brightness) (NRND) | Green    |
|----------------|----------|-----------------------|--------------------------|---------------------------------|----------|
| Common         |          |                       |                          |                                 |          |
| Anode          | LA-401VD | LA-401AD              | LA-401ED                 | LA-401XD                        | LA-401MD |
| Cathode        | LA-401VN | LA-401AN              | LA-401EN                 | LA-401XN                        | LA-401MN |

**●Absolute maximum ratings ( $T_a = 25^\circ\text{C}$ )**

| Parameter             | Symbol             | Red              | Red<br>(High brightness) | Orange<br>(High brightness) | Yellow<br>(High brightness)<br>(NRND) | Green            | Unit             |
|-----------------------|--------------------|------------------|--------------------------|-----------------------------|---------------------------------------|------------------|------------------|
|                       |                    | LA-401VD / VN    | LA-401AD / AN            | LA-401ED / EN               | LA-401XD / XN                         | LA-401MD / MN    |                  |
| Power dissipation     | $P_D$              | 320              | 520                      | 520                         | 520                                   | 480              | mW               |
| Power dissipation     | $P_D / \text{seg}$ | 40               | 65                       | 65                          | 65                                    | 60               | mW               |
| Forward current       | $I_F$              | 15               | 25                       | 25                          | 25                                    | 20               | mA               |
| Peak forward current  | $I_{FP}$           | 60 <sup>*1</sup> | 50 <sup>*2</sup>         | 50 <sup>*2</sup>            | 50 <sup>*2</sup>                      | 60 <sup>*1</sup> | mA               |
| Reverse voltage       | $V_R$              | 5                | 5                        | 5                           | 5                                     | 5                | V                |
| Operating temperature | $T_{opr}$          | -25 to +75       |                          |                             |                                       |                  | $^\circ\text{C}$ |
| Storage temperature   | $T_{stg}$          | -30 to +85       |                          |                             |                                       |                  | $^\circ\text{C}$ |

<sup>\*1</sup> Pulse width 1ms, duty 1 / 5

<sup>\*2</sup> Pulse width 0.1ms, duty 1 / 10

**●Electrical and optical characteristics ( $T_a = 25^\circ\text{C}$ )**

| Parameter               | Symbol          | Conditions          | Red  |      | Red<br>(High brightness) |      | Orange<br>(High brightness) |      | Yellow<br>(High brightness)<br>(NRND) |      | Green |      | Unit          |
|-------------------------|-----------------|---------------------|------|------|--------------------------|------|-----------------------------|------|---------------------------------------|------|-------|------|---------------|
|                         |                 |                     | Typ. | Max. | Typ.                     | Max. | Typ.                        | Max. | Typ.                                  | Max. | Typ.  | Max. |               |
| Forward voltage         | $V_F$           | $I_F = 10\text{mA}$ | 2.0  | 2.8  | 2.05*                    | 2.6* | 2.05*                       | 2.6* | 2.05*                                 | 2.6* | 2.1   | 2.8  | V             |
| Reverse current         | $I_R$           | $V_R = 3\text{V}$   | -    | 100  | -                        | 100  | -                           | 100  | -                                     | 100  | -     | 100  | $\mu\text{A}$ |
| Peak wavelength         | $\lambda_p$     | $I_F = 10\text{mA}$ | 650  | -    | 626*                     | -    | 610*                        | -    | 589*                                  | -    | 563   | -    | nm            |
| Spectral line halfwidth | $\Delta\lambda$ | $I_F = 10\text{mA}$ | 40   | -    | 18*                      | -    | 17*                         | -    | 15*                                   | -    | 40    | -    | nm            |

© Not designed for radiation resistance.

\* Shows the number on the condition of  $I_F = 20\text{mA}$ .

## ●Luminous intensity

| Parameter                             | $\lambda_p$ | Type     | Min. | Typ. | Max. | Unit |
|---------------------------------------|-------------|----------|------|------|------|------|
| Red                                   | 650         | LA-401VD | 5.6  | 16   | -    | mcd  |
|                                       |             | LA-401VN |      |      |      |      |
| Red<br>(High brightness)              | 626         | LA-401AD | 36   | 90   | -    | mcd  |
|                                       |             | LA-401AN |      |      |      |      |
| Orange<br>(High brightness)           | 610         | LA-401ED | 36   | 90   | -    | mcd  |
|                                       |             | LA-401EN |      |      |      |      |
| Yellow<br>(High brightness)<br>(NRND) | 589         | LA-401XD | 36   | 90   | -    | mcd  |
|                                       |             | LA-401XN |      |      |      |      |
| Green                                 | 563         | LA-401MD | 5.6  | 16   | -    | mcd  |
|                                       |             | LA-401MN |      |      |      |      |

© Condition  $I_F=10\text{mA}$ 

## ●Iv classification

| Parameter                   | Type                 | Item  | Iv classification |          | Unit |
|-----------------------------|----------------------|-------|-------------------|----------|------|
| Red                         | LA-401VD<br>LA-401VN | “ L ” | 5.6               | to 11    | mcd  |
|                             |                      | “ M ” | 9.0               | to 18    | mcd  |
|                             |                      | “ N ” | 14                | to 28    | mcd  |
|                             |                      | “ P ” | 22                | to 45    | mcd  |
|                             |                      | “ Q ” | 36                | to (71)  | mcd  |
| Red<br>(High brightness)    | LA-401AD<br>LA-401AN | “ Q ” | 36                | to 71    | mcd  |
|                             |                      | “ R ” | 56                | to 110   | mcd  |
|                             |                      | “ S ” | 90                | to 180   | mcd  |
|                             |                      | “ T ” | 140               | to 280   | mcd  |
|                             |                      | “ U ” | 220               | to (450) | mcd  |
| Orange<br>(High brightness) | LA-401ED<br>LA-401EN | “ Q ” | 36                | to 71    | mcd  |
|                             |                      | “ R ” | 56                | to 110   | mcd  |
|                             |                      | “ S ” | 90                | to 180   | mcd  |
|                             |                      | “ T ” | 140               | to 280   | mcd  |
|                             |                      | “ U ” | 220               | to (450) | mcd  |
| Green                       | LA-401MD<br>LA-401MN | “ L ” | 5.6               | to 11    | mcd  |
|                             |                      | “ M ” | 9.0               | to 18    | mcd  |
|                             |                      | “ N ” | 14                | to 28    | mcd  |
|                             |                      | “ P ” | 22                | to 45    | mcd  |
|                             |                      | “ Q ” | 36                | to (71)  | mcd  |

© Condition  $I_F=10\text{mA}$

●Electrical and optical characteristics curves

Fig.1 Forward Current vs. Forward Voltage




Fig.2 Relative Luminous Intensity vs. Forward Current




Fig.3 Relative Luminous Intensity vs. Case Temperature





Fig.4 Ratio of Maximum Tolerable Peak Current vs. Pulse Duration (I)



●Electrical and optical characteristics curves

Fig.5 Ratio of Maximum Tolerable Peak Current vs. Pulse Duration ( II )




Fig.6 Ratio of Maximum Tolerable Peak Current vs. Pulse Duration ( III )





Fig.7 Derating



## Notes

- 1) The information contained herein is subject to change without notice.
- 2) Before you use our Products, please contact our sales representative and verify the latest specifications.
- 3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.  
Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Products beyond the rating specified by ROHM.
- 4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.
- 5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.
- 6) The Products are intended for use in general electronic equipment (i.e. AV/OA devices, communication, consumer systems, gaming/entertainment sets) as well as the applications indicated in this document.
- 7) The Products specified in this document are not designed to be radiation tolerant.
- 8) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, servers, solar cells, and power transmission systems.
- 9) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.
- 10) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.
- 11) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.
- 12) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.
- 13) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.
- 14) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.



Thank you for your accessing to ROHM product informations.  
More detail product informations and catalogs are available, please contact us.

## ROHM Customer Support System

<http://www.rohm.com/contact/>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ROHM Semiconductor:](#)

[LA-401AD](#) [LA-401AN](#) [LA-401ED](#) [LA-401EN](#) [LA-401MD](#) [LA-401MN](#) [LA-401VD](#) [LA-401VN](#)