

SLR-342 series


LED, flat disk type, direct mount

The SLR-342 series LEDs are small, reflecting, high brightness single color LEDs.

Dimensions (Units : mm)

Features

- single LED per package
- diameter of lens = 3.1 mm
- height as low as 5.2 mm
- mounting pitch as small as 2.5 mm
- available in red, orange, yellow and green with choice of tinted diffused or tinted non-diffused lens
- available on tape for mounting by an automatic machine



Selection guide

Part no.	SLR-342VR	SLR-342DU	SLR-342YY	SLR-342MG
Color & wavelength	Red, 650 nm	Orange, 610 nm	Yellow, 585 nm	Green, 563 nm
Lens	Tinted diffused	Tinted diffused	Tinted diffused	Tinted diffused
Availability	standard	standard	standard	standard
Part no.	SLR-342VC	SLR-342DC	SLR-342YC	SLR-342MC
Color & wavelength	Red, 650 nm	Orange, 610 nm	Yellow, 585 nm	Green, 563 nm
Lens	Tinted non-diffused	Tinted non-diffused	Tinted non-diffused	Tinted non-diffused
Availability	standard	standard	standard	standard


Absolute maximum ratings ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Limits	Unit	Conditions
Power dissipation	MG & MC type	75	mW	
	All others	60	mW	
Forward current	MG & MC type	25	mA	
	All others	20	mA	
Peak forward current	I_{FP}	60	mA	Pulse width 1 ms, duty 20%
Reverse voltage	V_R	3	V	
Operating temperature	T_{opr}	-25 ~ +85	$^\circ\text{C}$	
Storage temperature	T_{stg}	-30 ~ +100	$^\circ\text{C}$	

Electro-optical characteristics ($T_a = 25^\circ\text{C}$)

Parameter		Symbol	Min	Typical	Max	Unit	Conditions
Forward voltage	Red Orange	V_F		2.0	3.0	V	$I_F = 10\text{ mA}$
	Yellow Green			2.1			
Reverse current		I_R			10	μA	$V_R = 3\text{ V}$
Peak wavelength		λ_p		Red 650 Orange 610 Yellow 585 Green 563		nm	$I_F = 10\text{ mA}$
Spectral half-width		$\Delta\lambda$		40		nm	$I_F = 10\text{ mA}$
Emission power half angle	Non-diffused	$2\theta_{1/2}$		40		deg	
	Diffused			40			

Figure 1 Luminous intensity vs wavelength



Luminous intensity

Part no.	Color	λ_p	Min	Typical	Max	Unit	Conditions
SLR-342VR	Red	650	3.6	10.0		mcd	For $I_F = 10\text{ mA}$
SLR-342VC			6.6	16.0		mcd	
SLR-342DU	Orange	610	3.6	10.0		mcd	
SLR-342DC			5.6	16.0		mcd	
SLR-342YY	Yellow	585	2.2	6.3		mcd	
SLR-342YC			5.6	16.0		mcd	
SLR-342MG	Green	563	5.6	16.0		mcd	
SLR-342MC			9.0	25.0		mcd	

Electrical characteristic curves 1 (Red)




Figure 2




Figure 3




Figure 4




Figure 5




Figure 6




Figure 7




Figure 8 Directional pattern (red)

Electrical characteristic curves 2 (Orange)




Figure 9




Figure 10




Figure 11




Figure 12




Figure 13




Figure 14




Figure 15 Directional pattern (orange)

Electrical characteristic curves 3 (Yellow)




Figure 16




Figure 17




Figure 18




Figure 19




Figure 20




Figure 21




Figure 22 Directional pattern (yellow)

Electrical characteristic curves 4 (Green)




Figure 23




Figure 24




Figure 25




Figure 26




Figure 27




Figure 28




Figure 29 Directional pattern (green)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ROHM Semiconductor:](#)

[SLR-342MCT32](#) [SLR-342MGT32](#) [SLR-342VCT32](#) [SLR-342VRT32](#) [SLR-342YYT32](#)