

## Sound Processor Series for FPD TVs

# **Sound Processor** with built-in Loudness **BD3869AF**





#### Description

BD3869AF is a 2ch sound processor with built-in loudness and volume control. It has low noise and low distortion due to the resistor ladder configuration. The IC current consumption is 3mA. The device is packaged in SOP18.

#### Features

- 1) Resistor ladder type circuit, used for Volume and Tone control, achieving low noises and low distortion and reduced switching shock sound.
- 2) The I<sup>2</sup>C BUS can control up to 3 devices. For Dolby digital applications, the 6ch can be used simultaneously.
- 3) High-performance functions are integrated into a compact package, idea for surround speakers and sub-woofers.
- 4) The center frequency and Q value in Bass characteristics can be changed by external components.

#### Applications

TV units such as DVD, PC, Hi-vision, Karaoke, digital broadcasting and CATV. Also for car and portable audio.

#### • Absolute maximum ratings (Ta=25°C)

Parameter	Symbol	Limits	Unit
Applied voltage	VCC	10.0	V
Input voltage	Vin	VCC+0.3~GND-0.3	V
Power Dissipation	Pd	680 <sup>*1</sup>	mW
Operating temperature	Topr	-40~+85 <sup>*2</sup>	°C
Storage temperature	Tastg	-55~+150	°C

\*1 Reduced by 5.5 mW/°C at 25°C or higher.

Thermal resistance  $\theta_{ja}$  = 181.8 (°C/W). (when Rohm standard board is mounted.)

Rohm standard board: Size:  $70 \times 70 \times 1.6 \text{ (mm}^3$ )

Material: FR4 glass-epoxy substrate (copper foil area: not more than 3%).

\*2 As long as voltage stays within operating voltage range, certain circuit operation is guaranteed in the operating temperature range.

Allowable power loss conditions are related to temperature, to which care must be taken. In addition though the standard value of its electrical characteristics cannot be guaranteed under the conditions other than those specified, basic functions are maintained.

#### • Operating voltage range

Parameter	Symbol	Min.	Тур.	Max.	Unit
Power supply voltage *3	VCC	5.3	9.0	9.5	V

Basic operation at Ta=25°C.

\*3 As long as temperature and operating voltage meet specifications

In addition, though the standard value of its electrical characteristics cannot be guaranteed under the conditions other than those specified, basic functions are maintained.

#### • Electric characteristics (BD3869AF)

Unless specified: Ta=25°C, VCC=9V, f=1kHz, Vin=1Vrms, Rg=600  $\Omega$ , RL=10k $\Omega$ , front volume = 0dB, Rear volume = 0dB, Bass = 0dB, Treble = 0dB, Loudness = OFF

	Deremeter	Baramatar Symbol Limits			1.1	Condition	
	Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
	Circuit current upon no signal	IQ	-	3	7	mA	Vin=0Vrms
	Maximum input voltage	VIM	2.2	2.5	-	Vrms	Front Volume = -6dB, THD(Vout)=1%
	Maximum output voltage	VOM	2.1	2.5	-	Vrms	THD=1%
	Voltage gain	GV	-2	0	2	dB	Gv=20log(Vout/Vin)
_	Channel balance	СВ	-1.5	0	1.5	dB	CB = Gv1-Gv2
ERA	Total harmonic distortion	THD	-	0.01	0.2	%	Vout=1Vrms, BPF=400-30kHz
GEN	Output noise voltage *	VNO	-	2.3	15	μVrms	BPF = IHF-A, Rg=0Ω
	Residual noise voltage *	VMNO	-	1.4	10	μVrms	Front Volume = -89dB Rear Volume = - $\infty$ , BPF = IHF-A, Rg=0 $\Omega$
	Cross talk *	СТ	70	95	-	dB	CT = 20log(Vin/Vout), BPF=IHF-A
	Input impedance	RIN	42	60	78	KΩ	In case of no external loudness
	Front volume control range	VATTF	-92	-89	-86	dB	VATT=20log(Vout/Vin), BPF=IHF-A
	Front volume switching step	SVFC	-	1	-	dB	
	Front volume set error 1	EVFC1	-2	0	+2	dB	0dB to -63dB
	Front volume set error 2	EVFC2	-3	0	+3	dB	-64dB to -89dB
	Rear volume control range	VATTR	-	-100	-90	dB	V <sub>ATT</sub> =20log(Vout/Vin), BPF=IHF-A
	Rear volume switching step 1	SVRC1	-	1	-	dB	0dB to -10dB
Ē	Rear volume switching step 2	SVRC2	-	2	-	dB	-10dB to -20dB
ILUN	Rear volume switching step 3	SVRC3	-	5	-	dB	-20dB to -35dB
20	Rear volume switching step 4	SVRC4	-	10	-	dB	-35dB to -45dB
	Rear volume switching step 5	SVRC5	-	15	-	dB	-45dB to -60dB
	Rear volume set error 1	EVRC1	-2	0	+2	dB	0dB to -35dB
	Rear volume set error 2	EVRC2	-3	0	+3	dB	-45dB , -60dB
		A <sub>TTMAX</sub>					Front Volume=-89dB
	Volume maximum attenuation		-	-114	-90	dB	Rear Volume=-∞
							A <sub>TTMAX</sub> =20log(Vout/Vin), BPF=IHP-A
	Provide a desta de la companya de la				. 47	dB	f=80Hz, Vin=100mVrms
	Bass boost control range	VBBMAX	+11	+14	+17	üВ	Bass = +14dB, V <sub>BBMAX</sub> =20log(Vout/Vin)
(0)		N	17	14	44	dB	f=80Hz, Vin=100mVrms
3AS(	Bass cut control range	VBCMAX	-17	-14	-11	ŭD.	Bass = -14dB, V <sub>BBMAX</sub> =20log(Vout/Vin)
-	Bass control step	SBC	-	2	-	dB	
	Bass set error (0dB-8dB)	EBS1	-2	0	2	dB	f=80Hz
	Bass set error (10dB-14dB))	EBS2	-3	0	3	dB	
	Treble boost control range	V <sub>TBMAX</sub>	+11	+14	+17	dB	f=15kHz, Vin=100mVrms Treble = +14dB, V <sub>TMAX</sub> =20log(Vout/Vin)
EBLE	Treble cut control range	V <sub>TCMAX</sub>	-17	-14	-11	dB	f=15kHz, Vin=100mVrms Treble = -14dB, V <sub>TMAx</sub> =20log(Vout/Vin)
TR	Treble control step	STC	-	2	-	dB	
	Treble set error (0dB-8dB)	ETS1	-2	0	2	dB	f=15kHz
	Treble set error (10dB-14dB)	ETS2	-3	0	3	dB	1
ō	ACK LOW level output voltage	VOL	0	-	0.4	V	Sink current =3mA
BU	SCL、SDA input HI level	VIHI	3.0	5	5.5	V	
I <sup>2</sup> C	SCL、SDA input LOW level	VILO	-0.5	0	1.5	V	

\* VP-9690A (Average value detection, effective value display) IHF-A filter by Matsushita Communication is used for measurement.

 $\ast\,\mbox{Phase}$  of I/O signal terminals is the same.

\* This IC is not designed to be radiation-resistant.

#### • Timing chart

Electric specifications and timing of bus line and I/O stages



Fig.-1 Timing definition on I<sup>2</sup>C BUS

#### Table 1: Characteristics of the SDA and SCL BUS lines for I<sup>2</sup>C BUS devices

	Parameter	Symbol	Standar I <sup>2</sup> C	Unit	
			Min.	Max.	
1	SCL clock frequency	f <sub>SCL</sub>	0	100	kHz
2	Bus free time between a STOP and START condition	t <sub>BUF</sub>	4.7	-	μs
3	Hold time (repeated) START condition. After this period, the first clock pulse is generated	$t_{HD};S_{TA}$	4.0	-	μs
4	LOW period of the SCL clock	t <sub>LOW</sub>	4.7	-	μs
5	HIGH period of the SCL clock	t <sub>HIGH</sub>	4.0	-	μs
6	Set-up time for a repeated START condition	t <sub>su;sta</sub>	4.7	-	μs
7	Data hold time	t <sub>HD;DAT</sub>	0*	-	μs
8	Data set-up time	t <sub>su; dat</sub>	250	-	ns
9	Rise time of both SDA and SCL signals	t <sub>R</sub>	-	1000	ns
10	Fall time of both SDA and SCL signals	t⊧	-	300	ns
11	Set-up time for STOP condition	t <sub>su;sто</sub>	4.0	-	μs
12	Capacitive load for each bus line	Cb	-	400	pF

Above numerical values all correspond to VIH min and VIL max levels (see Table 2).

\*The transmitter must internally provide at least 300 ns hold-time for SDA signals (at VIH min of SCL signals) in order to cross over undefined region at the fall-end of SCL.

#### Table 2: Characteristics of the SDA and SCL I/O stages for I<sup>2</sup>C-bus devices

	Parameter	Symbol	Standa I <sup>2</sup> C	Unit	
			Min.	Max.	
13	Low-level input voltage: fixed input levels	V <sub>IL</sub>	-0.5	1.0	V
14	Low-level input voltage: fixed input levels	V <sub>IH</sub>	2.3	-	V
15	Hysteresis of Schmitt trigger inputs: fixed input levels	V <sub>hys</sub>	n/a	n/a	V
16	Pulse width of spikes which must be suppressed by the input filter.	t <sub>SP</sub>	n/a	n/a	ns
17	Low-level output voltage (open drain): at 3mA sink current	V <sub>OL1</sub>	0	0.4	V
18	Output fall time from VIHmin. to VIHmax. with a bus capacitance from 10 pF to 400pF: with up to 3mA sink current at VOL1	t <sub>OF</sub>	-	250	ns
19	Input current each I/O pin with an input voltage between 0.4V and 0.9 VCCmax.	li	-10	10	μA
20	Capacitance for each I/O pin	Ci	-	10	pF

n/a = not applicable

#### Data format

#### Slave addresses

Since slave address can be changed by the setting of CHIP(7pin), a maximum of 3 pcs can be used at the same time.

CHIP(pin7) Condition	MSB Slave Address							
	A6	A5	A4	A3	A2	A1	A0	R/W
GND - 0.2×Vcc	1	0	0	0	0	0	0	0
0.4×Vcc - 0.6×Vcc	1	0	0	0	0	0	1	0
0.8×Vcc – Vcc	1	0	0	0	0	1	0	0

#### Select addresses

Set the voltage of 7pin to within the defined conditions.

Deremeter		MSB Select Address							LSB	
	Farameter	D7	D6	D5	D4	D3	D2	D1	D0	
0	Front Volume	0	0	0	0	0	0	0	0	
1	Rear Volume	0	0	0	0	0	0	0	1	
2	Bass / Treble	0	0	0	0	0	0	1	0	

Data format

	Daramatar	Select	MSB	Data LSB						LSB
	Falametei	Address	D7	D6 D5 D4				D2	D1	D0
0	Front Volume	00H	Loud	Front Volume B		Front Volume A				
1	Rear Volume	01H	*	Channel Select			Rear Volume			
2	Bass / Treble	02H		Bass Gain			Treble Gain			

#### Operation Notes

- 1. Numbers and data in entries are representative design values and are not guaranteed values of the items.
- Although ROHM is confident that the example application circuit reflects the best possible recommendations, be sure to verify circuit characteristics for your particular application. Modification of constants for other externally connected circuits may cause variations in both static and transient characteristics for external components as well as this Rohm IC. Allow for sufficient margins when determining circuit constants.
- 3. Absolute maximum ratings

Use of the IC in excess of absolute maximum ratings, such as the applied voltage or operating temperature range (Topr), may result in IC damage. Assumptions should not be made regarding the state of the IC (short mode or open mode) when such damage is suffered. A physical safety measure, such as a fuse, should be implemented when using the IC at times where the absolute maximum ratings may be exceeded.

4. GND potential

Ensure a minimum GND pin potential in all operating conditions. Make sure that no pins are at a voltage below the GND at any time, regardless of whether it is a transient signal or not.

#### 5. Thermal design

Perform thermal design, in which there are adequate margins, by taking into account the permissible dissipation (Pd) in actual states of use.

6. Short circuit between terminals and erroneous mounting

Pay attention to the assembly direction of the ICs. Wrong mounting direction or shorts between terminals, GND, or other components on the circuits, can damage the IC.

7. Operation in strong electromagnetic field

Using the ICs in a strong electromagnetic field can cause operation malfunction.





R	:	[Ω]
С	:	[F]

Terminal No.	Terminal name	Description of terminal	Terminal No.	Terminal name	Description of terminal
1	FT1	CH1 treble filter set terminal	10	SDA	I <sup>2</sup> C communication terminal
2	FT2	CH2 treble filter set terminal	11	SCL	I <sup>2</sup> C communication clock terminal
3	IN1	CH1 input terminal	12	VCC	Power supply terminal
4	LOUD1	CH1 loudness filter set terminal	13	OUT1	CH1 output terminal
5	IN2	CH2 input terminal	14	OUT2	CH2 output terminal
6	LOUD2	CH2 loudness filter set terminal	15	FB11	CH1 bus filter set terminal
7	CHIP	Chip select terminal	16	FB12	CH1 bus filter set terminal
8	FILTER	1/2VCC terminal	17	FB21	CH2 bus filter set terminal
9	GND	Ground terminal	18	FB22	CH2 bus filter set terminal

#### Reference data



100k

100k

100k

Fig.12 Cross talk vs Frequency

Fig.13 Maximum output voltage vs Load resistance



Reel

The contents described herein are correct as of April, 2006

The contents described herein are subject to change without notice. For updates of the latest information, please contact and confirm with ROHM CO.,LTD.

(Unit:mm)

Any part of this application note must not be duplicated or copied without our permission.

Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set. Any data, including, but not limited to application circuit diagrams and information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.LTD. disclaims any

warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.

Upon the sale of any such devices, other than for buyer's right to use such devices itself, resel or otherwise dispose of the same, implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by ROHM CO., LTD. is granted to any such buyer.

The products described herein utilize silicon as the main material.
 The products described herein are not designed to be X ray proof.

The products listed in this catalog are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys). Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

Excellence in Electronics



#### ROHM CO., LTD.

21, Saiin Mizosaki-cho, Ukyo-ku, Kyoto 615-8585, Japan TEL: (075)311-2121 FAX: (075)315-0172 URL http://www.rohm.com

Published by LSI Application Engineering Dept. Contact us for further information about the products.

Contact us for further information about th Atlanta U.S.A. /ROHM ELECTRONICS ATLANTA SALES OFFICE (DIVISION OF ROHM ELE.U.S.A., LLC)) TEL:+1(770)754-5972 FAX:+1(770)754-0901 Datas U.S.A. /ROHM ELECTRONICS DALLAS SALES OFFICE (DIVISION OF ROHM ELE.U.S.A., LLC)) TEL:+1(972)312-8818 FAX:+1(972)312-0330 San Diego U.S.A. /ROHM ELECTRONICS SAN DIEGO SALES OFFICE (DIVISION OF ROHM ELE.U.S.A., LLC) TEL:+1(858)825-3630 FAX:+1(858)825-3670 Germany / ROHM ELECTRONICS CMBH (URN) TEL:+48(2154)9210 FAX:+449(2154)821400 United Kingdom /ROHM ELECTRONICS CMBH (URN) TEL:+44(9)1398-36700 FAX:+449(2154)821400 United Kingdom /ROHM ELECTRONICS CMBH (URN) TEL:+44(9)1398-367070 FAX:+449(2154)821400 United Kingdom /ROHM ELECTRONICS CMBH (URN) TEL:+44(9)1398-367070 FAX:+449(2154)821400 United Kingdom /ROHM ELECTRONICS CMBH (URN) TEL:+439(21927)272 FAX:+439(2175-8971) Shanghai China / ROHM ELECTRONICS (HAANCHAI) CO, LTD. TEL:+852(2)7406282 FAX:+4562(2)875-8971 Balian China /ROHM ELECTRONICS (HAANCHAI) CO, LTD. TEL:+80(411)8230-8549 FAX:+86(2)18247-2066 Dalian /ROHM ELECTRONICS (HAANCHAI) CO, LTD. TEL:+80(411)8230-8549 FAX:+86(411)8230-8537

 Beijing China / BEIJING REPRESENTATIVE OFFICE

 TEL. +86(10)8525-2483

 Taiwan / ROHM ELECTRONICS TAIWAN CO., LTD.

 TEL. +88(2)8200-4966

 FAX: +88(2)8200-4966

 Korea / ROHM ELECTRONICS TAIWAN CO., LTD.

 TEL. +88(2)8200-4966

 Singapore / ROHM ELECTRONICS TAIWAN CO., LTD.

 TEL. +88(2)8200-4966

 Singapore / ROHM ELECTRONICS SALE CORPORATION

 TEL. +82(2)8182-700

 FAX: +86(2)850-32662

 Malaysia / ROHM ELECTRONICS (SALA TEL. LTD. (RES/REI)

 TEL: +465-6332-2322

 FAX: +66-6332-5662

 Philppines / ROHM ELECTRONICS (MALAYSIA) SDN. BHD.

 TEL: +40(3)7958-8335

 FAX: +60(3)7958-8337

 Philppines / ROHM ELECTRONICS (HALAYSIA) SALES CORPORATION

 TEL: +43(2)807-8372

 Philppines / ROHM ELECTRONICS (HALAYSIA) SALES CORPORATION

 TEL: +63(2)254-4890

 TeL: +66(2)254-4890

 FAX: +66(2)256-6334

Direction of feed

\*Orders are available in complete units only

1Pin

#### Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the
  product described in this document are for reference only. Upon actual use, therefore, please request
  that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or
  otherwise dispose of the same, no express or implied right or license to practice or commercially
  exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

It is our top priority to supply products with the utmost quality and reliability. However, there is always a chance of failure due to unexpected factors. Therefore, please take into account the derating characteristics and allow for sufficient safety features, such as extra margin, anti-flammability, and fail-safe measures when designing in order to prevent possible accidents that may result in bodily harm or fire caused by component failure. ROHM cannot be held responsible for any damages arising from the use of the products under conditions out of the range of the specifications or due to non-compliance with the NOTES specified in this catalog.

Thank you for your accessing to ROHM product informations. More detail product informations and catalogs are available, please contact your nearest sales office.

### **ROHM** Customer Support System

THE AMERICAS / EUROPE / ASIA / JAPAN

#### www.rohm.com

Contact us : webmaster@rohm.co.jp

Copyright © 2008 ROHM CO.,LTD. ROHM CO., LTD. 21 Saiin Mizosaki-cho, Ukyo-ku, Kyoto 615-8585, Japan TEL : +81-75-311-2121 FAX : +81-75-315-0172

Appendix1-Rev2.0

rohm

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ROHM Semiconductor: BD3869AF-E2