



### Main

|                               |                                                    |
|-------------------------------|----------------------------------------------------|
| Range of Product              | Hyde Park                                          |
| Sensor Type                   | Ultrasonic sensor                                  |
| Series name                   | Superprox 900                                      |
| Device short name             | SM950                                              |
| Sensor design                 | Cylindrical M30                                    |
| [Sn] nominal sensing distance | 26.25 ft (8 m)                                     |
| Type of sensing window        | Adjustable                                         |
| Material                      | Plastic                                            |
| Enclosure Material            | ULTEM                                              |
| Front material                | Glass epoxy                                        |
| Type of output signal         | Discrete                                           |
| Discrete output function      | 1 NO or 1 NC programmable                          |
| ISO thread                    | M30 x 1.5                                          |
| Wiring Technique              | 4-wire                                             |
| [Us] rated supply voltage     | 12...24 V DC overload and short-circuit protection |
| Supply voltage limits         | 10...28 V DC                                       |
| Discrete output type          | PNP                                                |
| Electrical connection         | 1 male connector M12 4 pins                        |
| Product Specific Application  | Discrete proximity                                 |

### Complementary

|                                 |                                                            |
|---------------------------------|------------------------------------------------------------|
| [Sd] sensing range              | 0.67...26.25 ft (0.203...8 m)                              |
| Maximum differential travel     | 0.50 in (12.7 mm)                                          |
| Blind zone                      | 7.99 in (203 mm)                                           |
| Transmission frequency          | 75 kHz                                                     |
| Repeat accuracy                 | 2.54 %                                                     |
| Beam angle                      | 10 °                                                       |
| Minimum size of detected object | Cylinder diameter 50.8 mm - up to 4572 mm sensing distance |
| Current Consumption             | 100 mA                                                     |
| Maximum switching current       | 100 mA reverse polarity protection                         |
| Height                          | 1.18 in (30 mm)                                            |
| Width                           | 1.70 in (43.18 mm)                                         |
| Depth                           | 1.18 in (30 mm)                                            |
| Length                          | 4.62 in (117.3 mm)                                         |
| Net Weight                      | 1.98 lb(US) (0.9 kg)                                       |

### Environment

|                                       |                                   |
|---------------------------------------|-----------------------------------|
| Product Certifications                | UL                                |
| Marking                               | CE                                |
| NEMA degree of protection             | NEMA 4X indoor use only)          |
| IP degree of protection               | IP67                              |
| Ambient air temperature for operation | -4...140 °F (-20...60 °C)         |
| Ambient Air Temperature for Storage   | -4...176 °F (-20...80 °C)         |
| Relative humidity                     | 100 % without condensation        |
| Vibration resistance                  | +/- 1 mm 10...55 Hz)IEC 60068-2-6 |

|                                      |                                          |
|--------------------------------------|------------------------------------------|
| Shock resistance                     | 30 gn in all 3 axes 11 ms IEC 60068-2-27 |
| Resistance to electromagnetic fields | 9.14 V/m (10 V/m) level 3 IEC 61000-4-3  |
| Resistance to fast transients        | 1 kV level 3 IEC 61000-4-4               |

### Ordering and shipping details

|                       |                                    |
|-----------------------|------------------------------------|
| Category              | 22490 - SENSORS-ULTRASONIC (XX5,6) |
| Discount Schedule     | DS2                                |
| GTIN                  | 03389119118194                     |
| Nbr. of units in pkg. | 1                                  |
| Package weight(Lbs)   | 0.26 lb(US) (0.12 kg)              |
| Returnability         | No                                 |
| Country of origin     | US                                 |

### Offer Sustainability

|                           |                                                                                                                                                                                                                                                                                                                                                                                   |
|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive         | Not applicable, out of EU RoHS legal scope                                                                                                                                                                                                                                                                                                                                        |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SM950A830089](#)