


**DIMENSIONS: mm**




**PART NUMBERING SYSTEM**

<b>3</b>	<b>0</b>	<b>1</b>	-	<b>T</b>	<b>F</b>	<b>R</b>	<b>A</b>	<b>2</b>	-	<b>1</b>	-	<b>1</b>	<b>0</b>	<b>0</b>	-	<b>R</b>	<b>C</b>
Prefix				Series						Tolerance		Value				Suffix (RoHS Compliant)	

SPECIFICATIONS :	
Power Rating (Watts)	0.0625W(1/16W)
Max.Working Voltage	50V
Max.Overload Voltage	100V
Dielectric Withstanding Voltage	100V
Temperature Range	-55°C~+155°C
Ambient Temperature	70°C


**DERATING CURVE**



**NOTES :**

- Nominal Resistance  
Effective figures of nominal resistance shall be in accordance
  - E-24 and E-96 series for 1%
  - E-24 series for 2% and 5%
- Resistance Range : 10Ω ~1MΩ
- RoHS Compliant

# 1% or 5% Thick Film Chip Resistor Array-Convex Terminal

Characteristics	Limits	Test Methods ( JIS C 5201-1 )
Temperature coefficient	Refer to item 5	<p>Natural resistance change per temp. degree centigrade.</p> $\frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (PPM/}^\circ\text{C)}$ <p>R1: Resistance value at room temperature (t<sub>1</sub>) R2: Resistance value at room temp.plus 100°C (t<sub>2</sub>)</p>
Short time overload	Resistance change rate is ± 5%(2.0 % + 0.1Ω) Max. ± 1%(1.0 % + 0.1Ω) Max.	Permanent resistance change after the application of a potential of 2.5 times RCWW for 5 seconds.
Insulation resistance	1,000M Ω or more	Apply 500V DC between protective coating and termination for 1 minute, then measure
Dielectric withstanding Voltage	No evidence of flashover mechanical damage,arcing or insulation break down	Clamped in the trough of a 90° metallic V-block and shall be tested at AC potential respectively specified in the table 1.for 60+10/-0 secs.
Terminal bending	Resistance change rate is ±(1.0% +0.05Ω) Max	Twist of Test Board: Y/X=5/90mm for 10 seconds
*Solderability	95% coverage Min.	Test temperature of solder: 245 ± 3°C Dipping them solder: 2-3 seconds (Sub-clause 4.17)
Soldering temp. reference	Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95% coverage Min.)	<p><b>Wave soldering condition:</b> (2 cycles Max.) Pre-heat: 100 ~ 120 °C, 30 ± 5 sec. Suggestion solder temp.: 235 ~ 255 °C, 10 sec. (Max.) Peak temp.: 260°C</p> <p><b>Reflow soldering condition:</b> (2 cycles Max.) Pre-heat: 150 ~ 180 °C, 90 ~ 120 sec. Suggestion solder temp.: 235 ~ 255 °C, 20 ~ 40 sec. Peak temp.: 260°C</p>  <p>Temperature profile for evaluation</p> <p><b>Hand soldering condition:</b> The soldering iron tip temperature should be less than 300°C and maximum contract time should be 5 sec.</p>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Xicon:

[301-TFRA2-5-100K-RC](#) [301-TFRA2-5-2K-RC](#) [301-TFRA2-5-4.3-RC](#) [301-TFRA2-5-5.6K-RC](#) [301-TFRA2-5-75-RC](#)  
[301-TFRA2-5-8.2K-RC](#) [301-TFRA2-5-18K-RC](#) [301-TFRA2-5-3.6K-RC](#) [301-TFRA2-5-43-RC](#) [301-TFRA2-5-15-RC](#)  
[301-TFRA2-5-120-RC](#) [301-TFRA2-5-3.3K-RC](#) [301-TFRA2-5-3.9K-RC](#) [301-TFRA2-5-47-RC](#) [301-TFRA2-5-27-RC](#)  
[301-TFRA2-5-33-RC](#) [301-TFRA2-5-51K-RC](#) [301-TFRA2-5-750-RC](#) [301-TFRA2-5-1K-RC](#) [301-TFRA2-5-2.2K-RC](#)  
[301-TFRA2-5-4.7K-RC](#) [301-TFRA2-5-430-RC](#) [301-TFRA2-5-68-RC](#) [301-TFRA2-5-30-RC](#) [301-TFRA2-5-1.8K-RC](#)  
[301-TFRA2-5-20K-RC](#) [301-TFRA2-5-220-RC](#) [301-TFRA2-5-22-RC](#) [301-TFRA2-5-3-RC](#) [301-TFRA2-5-680K-RC](#) [301-TFRA2-5-1.5K-RC](#)  
[301-TFRA2-5-220K-RC](#) [301-TFRA2-5-390-RC](#) [301-TFRA2-5-6.8K-RC](#) [301-TFRA2-5-100-RC](#) [301-TFRA2-5-10-RC](#)  
[301-TFRA2-5-200-RC](#) [301-TFRA2-5-240-RC](#) [301-TFRA2-5-5.1-RC](#) [301-TFRA2-5-2.7K-RC](#) [301-TFRA2-5-3.9-RC](#)  
[301-TFRA2-5-330-RC](#) [301-TFRA2-5-51-RC](#) [301-TFRA2-5-910-RC](#) [301-TFRA2-5-150-RC](#) [301-TFRA2-5-2-RC](#)  
[301-TFRA2-5-470-RC](#) [301-TFRA2-5-47K-RC](#) [301-TFRA2-5-820-RC](#) [301-TFRA2-5-82-RC](#) [301-TFRA2-5-10K-RC](#)  
[301-TFRA2-5-1M-RC](#) [301-TFRA2-5-270-RC](#) [301-TFRA2-5-4.7-RC](#) [301-TFRA2-5-360-RC](#) [301-TFRA2-5-36-RC](#)  
[301-TFRA2-5-39-RC](#) [301-TFRA2-5-560-RC](#) [301-TFRA2-5-56-RC](#) [301-TFRA2-5-680-RC](#) [301-TFRA2-5-7.5K-RC](#)  
[301-TFRA2-1-82-RC](#) [301-TFRA2-1-10K-RC](#) [301-TFRA2-1-13.7K-RC](#) [301-TFRA2-1-15.8K-RC](#) [301-TFRA2-1-4.75K-RC](#)  
[301-TFRA2-1-470-RC](#) [301-TFRA2-1-47-RC](#) [301-TFRA2-1-10-RC](#) [301-TFRA2-1-100K-RC](#) [301-TFRA2-1-2.2-RC](#)  
[301-TFRA2-1-5.36K-RC](#) [301-TFRA2-1-30.1K-RC](#) [301-TFRA2-1-7.5K-RC](#) [301-TFRA2-1-1K-RC](#) [301-TFRA2-1-3.9K-RC](#)  
[301-TFRA2-1-4.64K-RC](#) [301-TFRA2-1-3.57K-RC](#) [301-TFRA2-1-2.74K-RC](#) [301-TFRA2-1-20K-RC](#) [301-TFRA2-1-9.76K-RC](#)  
[301-TFRA2-1-100-RC](#) [301-TFRA2-1-2.21K-RC](#) [301-TFRA2-1-3.9-RC](#) [301-TFRA2-1-39-RC](#) [301-TFRA2-1-4.7K-RC](#)  
[301-TFRA2-1-56-RC](#) [301-TFRA2-1-150-RC](#) [301-TFRA2-1-22-RC](#) [301-TFRA2-1-910-RC](#)