


- Protects appliances that are vulnerable to vibration
- Connector cannot be accidentally pulled or vibrated out of the inlet
- Space availability/constraints
- Different angles for ease of access
- Space saving
- Release locking mechanism
- Prevents accidental disconnection



UL **KEMA** **RoHS** **CCC**



Maximum continuous operating voltage	250 VAC, 50/60 Hz
Nominal operating voltage	230 VAC
Rated currents	10 A for C13 plug
High potential test voltage	P→ PE 2000 VAC (1 min 50 Hz) P → N 2000 VAC (1 min 50 Hz)
Temperature range (operation and storage)	-25°C to +70°C
Protection category	IP 20 according IEC 60529
Flammability corresponding to	Plugs: UL 94 V-2 or better Cable: IEC 60332-1 Cat. F2
Connector (load side)	IEC C13 according to IEC/EN 60320-2-2 with IEC Lock UL 498, CSA C22.2 no. 42, Protection Class I
Connector (line side) and cables	Please refer to Available combinations IL 13 table

IL 13P-R-C14-H05-3100-X*	right angled IEC cable assembly with locking system for IEC C14 inlet
IL 13P-L-EU1-H05-3100-X*	left angled IEC cable assembly with locking system for IEC C14 inlet, EU version
IL 13P-U-SE-H05-3100-X*	up angled IEC cable assembly with locking system for IEC C14 inlet, stripped ends
IL 13P-D-UK1-H05-3100-X*	down angled IEC cable assembly with locking system for IEC C14 inlet, UK version

To compile a complete part number, please replace the X* with the required length (please refer to table below for available length per cable type):





- X* options = 200, 300 cm

Available Combinations IL 13

To compile a complete part number exchange the letters (IL13P-yyy-zzz-aaaa-bbb-c) with the data from the table below.

Load side IL13P IL13P (-R/-L/-D/-U)		Line side plug yyy		Cable type zzz		Cable core aaaa		Rating	Cable length* bbb		Cable color c		Cert.
IL13P-R	IEC C13 Female plug, right angled, lock	IEC C14, male, straight CEE 7/VII, right angled or straight Stripped Ends BS1363, right angled fused 5A	C14	H05VV-F	H05	3x1.00mm²	3100	250VAC 10A	100 cm	100	Black	-	CB KC KEMA SAA
			EU1						200 cm	200			
			SE						300 cm	300			
			UK1										
IL13P-L	IEC C13 Female plug, left angled, lock	IEC C14, male, straight CEE 7/VII, right angled or straight Stripped Ends BS1363, right angled fused 5A	C14	H05VV-F	H05	3x1.0mm²	3100	250VAC 10A	100 cm	100	Black	-	CB KC KEMA SAA
			EU1						200 cm	200			
			SE						300 cm	300			
			UK1										
IL13P-D	IEC C13 Female plug, down angled, lock	IEC C14, male, straight CEE 7/VII, right angled or straight Stripped Ends BS1363, right angled fused 5A	C14	H05VV-F	H05	3x1.0mm²	3100	250VAC 10A	100 cm	100	Black	-	CB KC KEMA SAA
			EU1						200 cm	200			
			SE						300 cm	300			
			UK1										
IL13P-U	IEC C13 Female plug, up angled, lock	IEC C14, male, straight CEE 7/VII, right angled or straight Stripped Ends BS1363, right angled fused 5A	C14	H05VV-F	H05	3x1.0mm²	3100	250VAC 10A	100 cm	100	Black	-	CB KC KEMA SAA
			EU1						200 cm	200			
			SE						300 cm	300			
			UK1										

*feet values are calculated to the matching length in cm



Headquarters, Global
Innovation and
Development

Switzerland
Schaffner Group
Industrie Nord
Nordstrasse 5
4542
Luterbach
+41 32 681 66 26
info@schaffner.com

To find your local partner within
Schaffner's global network [schaffner.com](https://www.schaffner.com)

© 2025 Schaffner Group

The content of this document has been carefully checked and understood. However, neither Schaffner nor its subsidiaries assume any liability whatsoever for any errors or inaccuracies of this document and the consequences thereof. Published specifications are subject to change without notice. Product suitability for any area of application must ultimately be determined by the customer. In all cases, products must never be operated outside their published specifications. Schaffner does not guarantee the availability of all published products. This disclaimer shall be governed by substantive Swiss law and resulting disputes shall be settled by the courts at the place of business of Schaffner Holding AG. Latest publications and a complete disclaimer can be downloaded from the Schaffner website. All trademarks recognized.

Sales and Application
Centers

China
Schaffner EMC Ltd. Shanghai
T20-3 C No 565 Chuangye Road Pudong district
201201
Shanghai
+86 2138139500
cschina@schaffner.com

Sweden
Schaffner EMC AB
Östermalmstrorg 1
114 42
Stockholm
+46 8 5050 2425
swedensales@schaffner.com

Switzerland
Schaffner EMV AG
Industrie Nord
Nordstrasse 5
4542
Luterbach
+41 32 681 66 26
switzerlandsales@schaffner.com

India
Schaffner India Pvt. Ltd
Regus World Trade Centre
WTC 22nd Floor Unit No 2238 Brigade
Gateway Campus 26/1 Dr. Rajkumar Road
Malleshwaram (W)
560055
Bangalore
+91 8067935355
indiasales@schaffner.com

Italy
Schaffner EMC S.r.l.
Via Ticino, 30
20900
Monza (MB)
+39 335 120 44 32
italysales@schaffner.com

Japan
Schaffner EMC K.K.
ISM Sangenjaya 7F
1-32-12 Kamiuma Setagaya-ku
154-0011
Tokyo
+81 3 5712 3650
japansales@schaffner.com

Singapore
Schaffner EMC Pte Ltd.
Blk 3015A Ubi Road 1 #05-09 Kampong Ubi
Industrial Estate
408705
Singapore
+65 63773283
singaporesales@schaffner.com

Finland
Schaffner Oy
Lohjanharjuntie 1109
08500
Lohja
+ 358 50 468 72 84
finlandsales@schaffner.com

France
Schaffner EMC S.A.S.
16-20 Rue Louis Rameau
95875
Bezons
+33 1 34 34 30 60
francesales@schaffner.com

Germany
Schaffner Deutschland GmbH
Ohiostr. 8
76149
Karlsruhe
+49 721 56910
germanysales@schaffner.com

Thailand
Schaffner EMC Co. Ltd.
Sathorn Square Tower
Room 3780 37FL 98 North-Sathorn Rd Silom
Bangrak
10500
Bangkok
+66 621056397
thailandsales@schaffner.com

United Kingdom
Schaffner Ltd.
Suite 1 Oakmede Place
Terrace Road
RG42 4JF
Binfield
+44 118 9770070
schaffner.uksales@te.com

United States
Schaffner EMC Inc.
52 Mayfield Avenue
Edison, New Jersey
+1 732 225 9533
usasales@schaffner.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schaffner:](#)

[IL13P-U-UK1-H05-3100-200](#) [IL13P-D-C14-H05-3100-100](#) [IL13P-U-C14-H05-3100-300](#) [IL13P-R-UK1-H05-3100-100](#)
[IL13P-L-SE-H05-3100-300](#) [IL13P-U-SE-H05-3100-300](#) [IL13P-D-C14-H05-3100-200](#) [IL13P-L-C14-H05-3100-300](#)
[IL13P-L-C14-H05-3100-100](#) [IL13P-D-EU1-H05-3100-100](#) [IL13P-U-C14-H05-3100-200](#) [IL13P-L-US1-SVT-3100-183](#)
[IL13P-R-SE-H05-3100-300](#) [IL13P-R-US1-SVT-3100-183](#) [IL13P-L-EU1-H05-3100-200](#) [IL13P-U-SE-H05-3100-200](#)
[IL13P-R-UK1-H05-3100-300](#) [IL13P-U-EU1-H05-3100-100](#) [IL13P-U-EU1-H05-3100-200](#) [IL13P-D-SE-H05-3100-100](#)
[IL13P-L-EU1-H05-3100-300](#) [IL13P-L-EU1-H05-3100-100](#) [IL13P-U-SE-H05-3100-100](#) [IL13P-D-UK1-H05-3100-100](#)
[IL13P-U-US1-SVT-3100-183](#) [IL13P-R-C14-H05-3100-300](#) [IL13P-D-SE-H05-3100-200](#) [IL13P-R-SE-H05-3100-100](#)
[IL13P-D-SE-H05-3100-300](#) [IL13P-L-UK1-H05-3100-200](#) [IL13P-L-UK1-H05-3100-100](#) [IL13P-R-EU1-H05-3100-200](#)
[IL13P-L-C14-H05-3100-200](#) [IL13P-R-EU1-H05-3100-300](#) [IL13P-L-SE-H05-3100-100](#) [IL13P-D-US1-SVT-3100-183](#)
[IL13P-R-UK1-H05-3100-200](#) [IL13P-L-UK1-H05-3100-300](#) [IL13P-U-UK1-H05-3100-300](#) [IL13P-R-SE-H05-3100-200](#)
[IL13P-L-SE-H05-3100-200](#) [IL13P-R-C14-H05-3100-100](#) [IL13P-U-C14-H05-3100-100](#) [IL13P-D-C14-H05-3100-300](#)
[IL13P-D-EU1-H05-3100-200](#) [IL13P-U-UK1-H05-3100-100](#) [IL13P-R-EU1-H05-3100-100](#)