



Main

Range of Product	Hyde Park
Sensor Type	Ultrasonic sensor
Series name	Superprox 900
Device short name	SM952
Sensor design	Cylindrical M30
[Sn] nominal sensing distance	6.56 ft (2 m)
Type of sensing window	Adjustable
Material	Plastic
Enclosure Material	ULTEM
Front material	Silicone rubber
Type of output signal	Discrete
Discrete output function	1 NO + 1 NC
ISO thread	M30 x 1.5
Wiring Technique	4-wire
[Us] rated supply voltage	12...24 V DC overload and short-circuit protection
Supply voltage limits	10...28 V DC
Discrete output type	NPN
Electrical connection	1 male connector M12 4 pins
Product Specific Application	Dual-level - pump-out latch w/alarm

Complementary

[Sd] sensing range	0.39...6.56 ft (0.12...2 m)
Maximum differential travel	0.10 in (2.5 mm)
Blind zone	4.72 in (120 mm)
Transmission frequency	200 kHz
Repeat accuracy	0.87 %
Beam angle	10 °
Minimum size of detected object	Cylinder diameter 1.6 mm - up to 305 mm sensing distance
Current Consumption	100 mA
Maximum switching current	100 mA reverse polarity protection
Height	1.18 in (30 mm)
Width	1.37 in (34.7 mm)
Depth	1.18 in (30 mm)
Length	3.78 in (96 mm)
Net Weight	0.57 lb(US) (0.26 kg)

Environment

Product Certifications	UL
Marking	CE
NEMA degree of protection	NEMA 4X indoor use only)
IP degree of protection	IP67
Ambient air temperature for operation	32...122 °F (0...50 °C)
Ambient Air Temperature for Storage	-4...176 °F (-20...80 °C)
Relative humidity	100 % without condensation
Vibration resistance	+/-1 mm 10...55 Hz)IEC 60068-2-6

Shock resistance	30 gn in all 3 axes 11 ms IEC 60068-2-27
Resistance to electromagnetic fields	9.14 V/m (10 V/m) level 3 IEC 61000-4-3
Resistance to fast transients	1 kV level 3 IEC 61000-4-4

Ordering and shipping details

Category	22490 - SENSORS-ULTRASONIC (XX5,6)
Discount Schedule	DS2
GTIN	03389119120401
Nbr. of units in pkg.	1
Package weight(Lbs)	0.26 lb(US) (0.12 kg)
Returnability	No
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SM952A458000](#)