



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	Battery recycling guide
--------------------	-------------------------

### Physical

Colour	Black
Depth	59.7 Cm
Height	12.2 Cm
Product weight	34.55 Kg
Width	19.7 Cm

### Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 % non-condensing
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Storage Relative Humidity	0...95 % Non-condensing

### Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Enclosed battery cartridge
Battery voltage	192 V
Battery type	Lead-acid battery
Additional information	Each APCRBC140 consists of 2 battery modules as shown in the product image.
Number of battery replacement quantity	1

## Packing Units

Package 1 Weight	37.27 Kg
Package 1 Height	22.6 Cm
Package 1 width	40.9 Cm
Package 1 Length	78.1 Cm
Number of Units in Package 3	20

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and-lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Commercialised**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[APCRBC140](#)