

# AR3150SP1

## NetShelter SX 42U 750mm Wide x 1070mm Deep Enclosure - 1250 lbs. Shock Packaging



### Overview

Presentation	Wide enclosure with increased cable management options for high density server and networking applications. 42U height to easily roll through doorways. Additional shock packaging for shipping equipment weighing up to 1250lbs/568kg.
Lead time	Special Order - Call for Quoted Lead Times

### General

Provided equipment	Baying hardware Key(S) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels
--------------------	--

### Physical

Maximum Mounting Depth	36.02 in (91.49 cm)
Number of rack unit	42U
Minimum Mounting Depth	7.40 in (18.8 cm)
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Color	Black
Depth	42.13 in (107 cm)
Rack width	19"
Height	78.39 in (199.1 cm)
Net Weight	343.81 lb(US) (155.95 kg)
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3750 lb(US) (1700.97 kg) static
Width	29.53 in (75 cm)

### Conformance

Standards	UL 60950 EIA-310E
-----------	----------------------




### Ordering and shipping details

GTIN	00731304247500
Package weight(Lbs)	378.89 lb(US) (171.86 kg)

## Packing Units

Package 1 Height	83.27 in (211.5 cm)
Package 1 width	35.51 in (90.2 cm)
Package 1 Length	48.11 in (122.2 cm)
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AR3150SP1](#)