

AR3350X609

APC Netshelter SX, Server Rack Enclosure,
42U, without Sides, Black, 1991H x 750W x
1200D mm



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Baying hardware Key(S) Leveling feet Mounting Hardware Pre-installed casters
--------------------	--

Physical

Maximum Mounting Depth	41.26 in (104.8 cm)
Number of rack unit	42U
Minimum Mounting Depth	10.31 in (26.19 cm)
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof
Color	Black
Depth	47.24 in (120 cm)
Rack width	19"
Height	78.39 in (199.1 cm)
Product Weight	355.74 lb(US) (161.36 kg)
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3000 lb(US) (1360.78 kg) static
Width	29.53 in (75 cm)

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	00731304293682
Package weight(Lbs)	403.84 lb(US) (183.18 kg)

Packing Units

Package 1 Height	83.39 in (211.8 cm)
Package 1 width	33.50 in (85.1 cm)
Package 1 Length	52.52 in (133.4 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AR3350X609](#)