



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Kw Rating	330 W
Rated power in VA	600 VA
Nb of power socket outlets	5 NEMA 5-15R 2 NEMA 5-15R surge
Main Output Voltage	120 V
Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	5 ft (1.52 m)

General

Provided equipment	User Manual
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Depth	4.13 in (10.5 cm)
Height	5.47 in (13.9 cm)
Mounting preference	No preference
Net Weight	7.69 lb(US) (3.49 kg)
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No
Width	10.79 in (27.4 cm)

Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Efficiency at full load	92...139 V

Output

Max Configurable Power (Watts)	330 W
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Topology	Standby
Waveform Type	Stepped approximation to a sinewave
Maximum configurable power in VA	600 VA
Transfer Time	6ms typical : 10ms maximum

Conformance

Product Certifications	California (CEC) Battery Charger CTUVus NOM
Standards	FCC Part 15 class B UL 1778
Equipment protection policy	Lifetime : \$75000

Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Relative Humidity	0...90 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	35 dBA
Heat dissipation	16 Btu/h

Batteries & Runtime

Battery Type	Lead-Acid battery
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	10 h
Battery Charge Power (Watts)	7 W rated
Battery power in VAH	78 VAh capacity 66 VAh runtime
Battery life	3...5 year(s)
Extendable Run Time	0

Communications & Management

Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	490 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m
Let Through Voltage Rating	5 V

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304325116
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

Packing Units

Package 1 Height	7.72 in (19.6 cm)
Package 1 width	14.29 in (36.3 cm)
Package 1 Length	6.61 in (16.8 cm)
SCC14	10731304325113
Number of Units in Package 2	2
Package 2 Weight	18.52 lb(US) (8.40 kg)
Package 2 Height	8 in (203.20 mm)
Package 2 width	13 in (330.20 mm)
Package 2 Length	14 in (355.60 mm)
Number of Units in Package 3	60
Package 3 Weight	504.86 lb(US) (229 kg)
Package 3 Height	42.05 in (106.8 cm)
Package 3 width	29.80 in (75.7 cm)
Package 3 Length	41.54 in (105.5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[BE600M1](#)