

DPE32U7

Easy TeSys DPE IEC contactor, 32 A, 3 P, 15 HP at 480 VAC, nonreversing, 240 V 50/60 Hz coil



Main

Range	Easy TeSys
Product name	Easy TeSys DPE
Product or Component Type	Contactor
Device short name	DPE
Contactor application	Resistive load Motor control

Complementary

Utilisation category	AC-4 AC-1 AC-3
Poles description	3P
Pole contact composition	3 NO
Maximum Operational Voltage	Power circuit <= 690 V AC 25...400 Hz Power circuit <= 300 V DC
[Ie] rated operational current	32 A 140 °F (60 °C) <= 440 V AC AC-3 power circuit 40 A 140 °F (60 °C) <= 440 V AC AC-1 power circuit
Motor power kW	5.5 kW 220...230 V AC 50/60 Hz 11 kW 380...400 V AC 50/60 Hz 11 kW 415...440 V AC 50/60 Hz 15 kW 500 V AC 50/60 Hz
Maximum Horse Power Rating	3 Hp 230/240 V at AC 50/60 Hz for 1 phase 2 Hp 115 V at AC 50/60 Hz for 1 phase 7.5 Hp 230/240 V at AC 50/60 Hz for 3 phase 15 hp 460/480 V at AC 50/60 Hz for 3 phase
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	240 V AC 50/60 Hz
Auxiliary contact composition	1 NO
[Uimp] rated impulse withstand voltage	6 kV IEC 60947
Overvoltage category	III
[Ith] conventional free air thermal current	10 A 140 °F (60 °C) signalling circuit 40 A 140 °F (60 °C) power circuit
Irms rated making capacity	140 A AC signalling circuit IEC 60947-5-1 250 A DC signalling circuit IEC 60947-5-1 450 A 440 V power circuit IEC 60947
Rated breaking capacity	450 A 440 V power circuit IEC 60947
Associated fuse rating	10 A gG signalling circuit IEC 60947-5-1 63 A gG <= 690 V type 1 power circuit 40 A gG <= 690 V type 2 power circuit
Average impedance	2 mOhm - Ith 40 A 50 Hz power circuit
[Ui] rated insulation voltage	Power circuit 690 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1
Electrical durability	1 Mcycles 32 A AC-3 <= 440 V 0.6 Mcycles 40 A AC-1 <= 440 V

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the Schneider Electric group. It is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Power dissipation per pole	3.2 W AC-1 1.25 W AC-3
Mounting Support	Rail Plate
Connections - terminals	Power circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) flexible without cable end Power circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) flexible without cable end Power circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) flexible with cable end Power circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) flexible with cable end Power circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) solid without cable end Power circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) solid without cable end Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) flexible without cable end Control circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) flexible without cable end Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) flexible with cable end Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) flexible with cable end Control circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) solid without cable end Control circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) solid without cable end
Tightening torque	Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2 Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2
Operating time	12...22 ms closing 4...19 ms opening
Safety reliability level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	10 Mcycles
Maximum operating rate	3600 cyc/h 140 °F (60 °C)
Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.3...0.6 Uc 50/60 Hz 158 °F (70 °C)) Operational 0.8...1.1 Uc 50 Hz 140 °F (60 °C)) Operational 0.85...1.1 Uc 60 Hz 140 °F (60 °C)) Operational 1...1.1 Uc 50/60 Hz 158 °F (70 °C))
Inrush power in VA	70 VA 60 Hz 0.75 68 °F (20 °C)) 70 VA 50 Hz 0.75 68 °F (20 °C))
Hold-in power consumption in VA	7.5 VA 60 Hz 0.3 68 °F (20 °C)) 7 VA 50 Hz 0.3 68 °F (20 °C))
Auxiliary contacts type	Mechanically linked 1 NO IEC 60947-5-1
Signalling circuit frequency	25...400 Hz
Minimum switching current	5 mA signalling circuit
Minimum switching voltage	17 V signalling circuit
Non-overlap time	1.5 Ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Insulation resistance	> 10 MOhm signalling circuit
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz) Vibrations contactor closed 4 Gn, 5...300 Hz) Shocks contactor open 10 Gn for 11 ms) Shocks contactor closed 15 Gn for 11 ms)
Height	3.35 in (85 mm)
Width	1.77 in (45 mm)
Depth	3.62 in (92 mm)
Net Weight	0.82 lb(US) (0.37 kg)

Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 60947-4-1
Product Certifications	UL CSA
Heat dissipation	2...3 W 50/60 Hz
IP degree of protection	IP20 front face IEC 60529
Pollution degree	3
Protective treatment	TH IEC 60068-2-30
Ambient Air Temperature for Operation	-40...140 °F (-40...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	0...6561.68 ft (0...2000 m)
Flame retardance	V1 conforming to UL 94
Fire resistance	1562 °F (850 °C) IEC 60695-2-1

Ordering and shipping details

Category	22362-EASY TESYS DPE1
Discount Schedule	I13
GTIN	3606481063250
Nbr. of units in pkg.	1
Package weight(Lbs)	14.74 oz (418.0 g)
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.62 in (9.2 cm)
Package 1 width	1.77 in (4.5 cm)
Package 1 Length	3.35 in (8.5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DPE32U7](#)