



Main

Range	TeSys
Device short name	GV4A
Product or component type	Auxiliary contact block
Device application	Signalling
Range compatibility	TeSys GV4 multifunction circuit breaker
Mounting location	Right side
Mounting mode	Clipped
Pole contact composition	2 NO + 2 NC

Complementary

[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
[Ue] rated operational voltage	24...250 V AC 24...250 V DC
[Ith] conventional free air thermal current	5 A
Associated fuse rating	5 A gG conforming to IEC 60947-5-1
Mechanical durability	100000 Cycles
Minimum switching current	2 MA
Minimum switching voltage	17 V
Rated operational power in VA	400 VA at 230...240 V AC-12
Rated operational power in W	50 W at 24 V DC-12

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	150 G
Package 1 Height	3 Cm
Package 1 width	9 Cm
Package 1 Length	15.6 Cm
Unit Type of Package 2	S02
Number of Units in Package 2	18
Package 2 Weight	3 Kg
Package 2 Height	15 Cm
Package 2 width	30 Cm
Package 2 Length	40 Cm

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status :	Commercialised
-----------------------	----------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV4ADM1111](#)