



Overview

Presentation	Modular battery cabinet for extended runtime for UPSs with internal batteries. The cabinet is supplied without batteries, so modular battery strings must be purchased separately. Up to 9 battery strings can be installed and monitored in the cabinet.
Lead time	Usually Ships within 2 Weeks

General

Provided equipment	Installation guide
--------------------	--------------------

Physical

Surface finish	Gloss level 85%
Color	White
Depth	33.35 in (84.7 cm)
Height	77.56 in (197 cm)
Net Weight	903.90 lb(US) (410 kg)
Width	21.65 in (55 cm)

Conformance

Standards	FCC Part 15 class A
-----------	---------------------

Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative humidity	0...95 % non-condensing
Ambient air temperature for storage	5...104 °F (-15...40 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	10...80 % Non-condensing

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cabinet
Battery type	VRLA
Battery Volt-Amp-Hour Capacity	0 VAh

Ordering and shipping details

Package weight(Lbs)	454.15 lb(US) (206 kg)
---------------------	------------------------

Packing Units

Package 1 Height	81.97 in (208.2 cm)
Package 1 width	29.72 in (75.5 cm)
Package 1 Length	39.76 in (101 cm)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GVSMODBC9](#)