



Main

Range of product	Harmony iPC
Product or component type	Modular box PC
Device short name	Modular BOX PC basic Optimized
Operating system	Windows 10 IoT Enterprise 64 bit multi-language
Software package	Node-RED and system nodes restore IIoT Wiring Operating System Restore McAfee white listing installer cyber security license not included EcoStruxure secure connect advisor annual subscription cyber security license not included EcoStruxure Operator Terminal Expert run time HMI license not included EcoStruxure machine SCADA expert run time HMI/SCADA on configured offer-only EcoStruxure augmented operator advisor server augmented operator license not included

Complementary

Range compatibility	IDisplay Modular Display HMIDM
Accessory / separate part destination	PC panel on HMIDM modular display
Mounting location	Book mounting Flat mounting Wall mounting
Processor name	Intel Atom E3930 upto 1.8 GHz
Data storage equipment	64 GB eMMC (soldered)
Memory description	4 GB RAM DDR3 internal (not expandable)
Number of slots	1 slot(s) for mini PCI Express full-size with optional interface plate,
Display resolution	3200 x 2000 pixels at 60 Hz
Watchdog timer	1...255 Ms
Type of cooling	Fanless
Electrical connection	Screw connector, connector type: pin, 1 way, circuit application: ground - location: bottom Connector, connector type: SMA, 3 ways - location: top
Integrated connection type	Display port with 1 on front Ethernet with 2 RJ45 Realtek 8111G, transmission rate: 10/100/1000 Mbps on-bottom IEEE 1588 not supported COM1 serial link for battery backup with 1 male SUB-D 9 RS232/422/485 on bottom non-isolated USB 2.0 port with 1.0 USB type A, transmission rate: 480 Mbit/s on bottom USB 3.0 port with 1.0 USB type A, transmission rate: 5 Gbit/s on bottom TPM connector Ver 2.0 for cyber security - hardware encryption TPM module HMIYMINATPM201 to be installed/default installed on motherboard
Cyber secured boot	Secure password boot UEFI
[Us] rated supply voltage	24 V DC power supply 100...240 V AC power supply
Supply voltage limits	9.6...28.8 V

Inrush current	2.03 A
Power consumption in W	20.0 W (box) 15.0 W (with 4:3 12" display HMIDM6421) 16.0 W (with Wide 12" display HMIDM6521) 17.0 W (with 4:3 15" display HMIDM7421) 19.0 W (with Wide 15" display HMIDM7521) 20.0 W (with Wide 19" display HMIDM9521) 21.0 W (with Wide 22" display HMIDMA521)
Control type	ON/OFF button
Depth	46 Mm
Height	150 Mm
Width	187 Mm
Product weight	1.2 Kg
Number of slots available for expansion	1.0 slot(s) for mini PCIe





Environment

Standards	Class A group 1 EN 55011 EN 61000-6-4 EN 61131-2 FCC part 15 UL 60950
Product certifications	CE CULus UL 60950 for IT equipments EAC CCC RCM
Quality labels	CE
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive
IP degree of protection	IP40 conforming to IEC 60529
Electromagnetic compatibility	Immunity to high frequency interference conforming to IEC 61000-4 Disturbing field emission class A conforming to EN 55011 Conducted and radiated emissions class A conforming to EN 55022
Ambient air temperature for storage	-20...60 °C conforming to IEC 60068-2-2
Relative humidity	10...95 % non-condensing conforming to EN/IEC 60068-2-30
Ambient air temperature for operation	0...50 °C (by default) on mini PCIe conforming to EN/IEC 60068-2-2 0...50 °C flat mounting on mini PCIe 0...45 °C 0...45 °C flat mounting
Operating altitude	2000 m conforming to EN/IEC 60664-1
Vibration resistance	2 gn (f = 5...500 Hz) eMMC

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.666 Kg
Package 1 Height	8.4 Cm
Package 1 width	21.8 Cm
Package 1 Length	32.2 Cm
Unit Type of Package 2	S03
Number of Units in Package 2	6
Package 2 Weight	10.76 Kg
Package 2 Height	30 Cm
Package 2 width	30 Cm
Package 2 Length	40 Cm

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIBMIEA5DD1E01](#)