

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys U
Device short name	LU2B
Product or component type	Reversing power base
Device application	Motor
Poles description	3P
Suitability for isolation	Yes
[I _{th}] conventional free air thermal current	12 A
Utilisation category	AC-44 AC-41 AC-43
[U _c] control circuit voltage	48 V AC 50/60 Hz 48...72 V DC

Complementary

Auxiliary contact composition	1 NO + 1 NC
Auxiliary contacts type	Type linked contacts (1 NO + 1 NC) conforming to IEC 60947-4-1 Type mirror contact (1 NC) state of the power conforming to draft IEC 60947-1
System Voltage	230 V 440 V 500 V 690 V
Network frequency	40...60 Hz
[I _e] rated operational current	12 A at ≤ 440 V 12 A at 500 V 9 A at 690 V
[I _{cs}] rated service breaking capacity	10 kA 500 V 4 kA 690 V 50 kA 230 V 50 kA 440 V
Control circuit voltage limits	29 V 48 V AC drop-out 29 V 48...72 V DC drop-out 38.5...72 V 48 V AC in operation 38.5...93 V 48...72 V DC in operation
Typical current consumption	2300 mA at 48...72 V DC I maximum while closing 2300 mA at 48 V AC I maximum while closing
Inrush restraint duration	15 ms DC network 25 ms AC network 50/60 Hz
Safety reliability level	B10d 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Operating time	150 ms with change of direction power circuit 35 ms opening control circuit 60 ms closing control circuit 75 ms without change of direction power circuit
Mechanical durability	15000000 cycles
Operating rate	60 cyc/mn
[U _i] rated insulation voltage	600 V conforming to CSA C22.2 No 14 600 V conforming to UL 508 690 V conforming to IEC 60947-1 3
[U _{imp}] rated impulse withstand voltage	6 kV conforming to IEC 60947-6-2

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Safe separation of circuit	400 V SELV between the control and auxiliary circuits conforming to IEC 60947-1 appendix N 400 V SELV between the control or auxiliary circuit and the main circuit conforming to IEC 60947-1 appendix N
Connections - terminals	Power circuit: screw clamp terminals 2 cable 0...0.01 in ² (1.5...6 mm ²) - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable 0...0 in ² (0.34...1.5 mm ²) - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable 0...0 in ² (0.75...1.5 mm ²) - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable 0...0 in ² (0.75...1.5 mm ²) - cable stiffness: rigid - without cable end Control circuit: screw clamp terminals 2 cable 0...0 in ² (0.34...1.5 mm ²) - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 2 cable 0...0 in ² (0.75...1.5 mm ²) - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable 0...0 in ² (0.75...1.5 mm ²) - cable stiffness: rigid - without cable end Power circuit: screw clamp terminals 1 cable 0...0.02 in ² (1...10 mm ²) - cable stiffness: rigid - without cable end Power circuit: screw clamp terminals 1 cable 0...0.01 in ² (1...6 mm ²) - cable stiffness: flexible - with cable end Power circuit: screw clamp terminals 1 cable 0...0.02 in ² (2.5...10 mm ²) - cable stiffness: flexible - without cable end Power circuit: screw clamp terminals 2 cable 0...0.01 in ² (1...6 mm ²) - cable stiffness: flexible - with cable end Power circuit: screw clamp terminals 2 cable 0...0.01 in ² (1...6 mm ²) - cable stiffness: rigid - without cable end
Tightening torque	Control circuit: 7.08...10.62 lbf.in (0.8...1.2 N.m) - with screwdriver 0.2 in (5 mm) flat Control circuit: 7.08...10.62 lbf.in (0.8...1.2 N.m) - with screwdriver 0.2 in (5 mm) Philips no 1 Power circuit: 16.81...22.12 lbf.in (1.9...2.5 N.m) - with screwdriver 0.24 in (6 mm) flat Power circuit: 16.81...22.12 lbf.in (1.9...2.5 N.m) - with screwdriver 0.24 in (6 mm) Philips No 2
Width	1.77 in (45 mm)
Height	8.82 in (224 mm)
Depth	4.96 in (126 mm)
Product weight	2.8 lb(US) (1.27 kg)

Environment

Heat dissipation	3 W control circuit with LUCA, LUCB, LUCC, LUCD 1.8 W control circuit with LUCM
Immunity to microbreaks	3 ms
Immunity to voltage dips	70 % 500 ms conforming to IEC 61000-4-11
Product certifications	CCC ABS ASEFA BV UL GL GOST CSA ATEX LROS (Lloyds register of shipping) DNV
Standards	CSA C22.2 No 14 type E EN 60947-6-2 IEC 60947-6-2 UL 508 type E with phase barrier
IP degree of protection	IP20 front panel and wired terminals conforming to IEC 60947-1 IP20 other faces conforming to IEC 60947-1 IP40 front panel outside connection zone conforming to IEC 60947-1
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	-13...140 °F (-25...60 °C) with LUCM -13...158 °F (-25...70 °C) with LUCA, LUCB, LUCC, LUCD
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Fire resistance	1202 °F (650 °C) conforming to IEC 60695-2-12 1760 °F (960 °C) parts supporting live components conforming to IEC 60695-2-12
Operating altitude	6561.68 ft (2000 m)

Shock resistance	10 gn power poles open conforming to IEC 60068-2-27 15 gn power poles closed conforming to IEC 60068-2-27
Vibration resistance	2 gn 5...300 Hz power poles open conforming to IEC 60068-2-27 4 gn 5...300 Hz power poles closed conforming to IEC 60068-2-27
Resistance to electrostatic discharge	8 kV level 3 in open air conforming to IEC 61000-4-2 8 kV level 4 on contact conforming to IEC 61000-4-2
Resistance to radiated fields	9.14 V/yd (10 V/m) 3 conforming to IEC 61000-4-3
Resistance to fast transients	2 kV class 3 serial link conforming to IEC 61000-4-4 4 kV class 4 all circuits except for serial link conforming to IEC 61000-4-4
Non-dissipating shock wave	1 kV serial mode conforming to IEC 60947-6-2 2 kV common mode conforming to IEC 60947-6-2
Immunity to radioelectric fields	10 V conforming to IEC 61000-4-6

Ordering and shipping details

Category	22396 - TESYS U - SELF PRCTD STARTER (LUB)
Discount Schedule	I11
GTIN	003389110362954
Nbr. of units in pkg.	1
Package weight(Lbs)	2.79
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0846 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LU2B12ES](#)