



Main

Range of Product	Harmony GTU
Product or Component Type	Base unit
Device short name	Open Box
Operating system	Windows Embedded 7
Software package	Internet Explorer Vijeo Citect web client Vijeo Designer run time .NET framework 4.0 Adobe PDF reader Multimedia player Office reader VNC client/server

Complementary

Range Compatibility	Harmony GTU
Processor name	Intel X86
Data storage equipment	32 GB CFast card
Port Ethernet	10BASE-T/100BASE-TX/1000BASE-T
Memory description	512 kB NVRAM backup memory 2 GB RAM internal
Type of cooling	Natural convection
Integrated connection type	Ethernet TCP/IP 2 RJ45 COM1 serial link RJ45 RS485 110...115200 bit/s COM2 serial link SUB-D 9 RS232C/RS422/RS485 110...115200 bit/s Auxiliary port terminal block Expansion unit fieldbus card USB 2.0 port mini B USB DVI-D video port DVI-D Microphone mini-jack USB 2.0 port 3 USB type A
Communication Port Protocol	Modbus Modbus TCP/IP Uni-Telway
[Us] rated supply voltage	12...24 V DC power supply
Depth	1.77 in (45 mm)
Height	5.16 in (131 mm)
Width	7.40 in (188 mm)
Net Weight	1.98 lb(US) (0.9 kg)
Number of slots available for expansion	1 fieldbus card

Environment

Standards	CSA C22.2 No 142 ANSI/ISA 12-12-01 UL 508 Class I division 2 CSA C22.2 No 213 IEC 61132-2
Product certifications	CE CULus ATEX IEC-Ex RCM GL KC CUL EAC ABS BV CCS DNV LR RINA
Pollution degree	2 EN 61131-2 Ed.3
Electromagnetic compatibility	Electrostatic discharge immunity test EN/IEC 61000-4-2 level 3
Ambient air temperature for storage	-4...140 °F (-20...60 °C)
Relative Humidity	10...90 % non-condensing
Ambient air temperature for operation	32...140 °F (0...60 °C)
Operating altitude	2000
Vibration resistance	3.5 mm constant amplitude 5...9 Hz) EN/IEC 61131-2 9.8 m/s² 9...150 Hz) EN/IEC 61131-2

Ordering and shipping details

Category	22567 - MAGELIS HMI GTU
Discount Schedule	MC2
GTIN	3606481213785
Nbr. of units in pkg.	1
Package weight(Lbs)	2.78 lb(US) (1.262 kg)
Returnability	Yes
Country of origin	CN

Packing Units


Unit Type of Package 1	PCE
Package 1 Height	5.16 in (131 mm)
Package 1 width	8.27 in (210 mm)
Package 1 Length	10.24 in (260 mm)
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Weight	12.92 lb(US) (5.862 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)
Unit Type of Package 3	P12
Number of Units in Package 3	48
Package 3 Weight	174.92 lb(US) (79.344 kg)
Package 3 Height	31.50 in (80 cm)
Package 3 width	47.24 in (120 cm)
Package 3 Length	41.34 in (105 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions

External Dimensions



- 1 Front
- 2 Left
- 3 Bottom

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIG5U2](#)