

# RSB2A080M7PV

Harmony, Interface plug-in relay pre-assembled, 8 A, 2 CO, with LED, with protection circuit, 220 V AC



## Main

|                                              |                                         |
|----------------------------------------------|-----------------------------------------|
| Range of Product                             | Harmony Electromechanical Relays        |
| Series name                                  | Interface relay                         |
| Product or Component Type                    | Pre-assembled plug-in relay with socket |
| Device short name                            | RSB                                     |
| Contacts type and composition                | 2 C/O                                   |
| Contact operation                            | Standard                                |
| [Uc] control circuit voltage                 | 220 V AC 50/60 Hz                       |
| [Ithe] conventional enclosed thermal current | 8 A -40...104 °F (-40...40 °C)          |
| Status LED                                   | 1 LED                                   |
| Control Type                                 | Without                                 |

## Complementary

|                                        |                                                                              |
|----------------------------------------|------------------------------------------------------------------------------|
| Average coil resistance                | 30000 Ohm AC 20 °C +/- 15 %                                                  |
| [Ue] rated operational voltage         | 176...242 V AC 50/60 Hz                                                      |
| [Ui] rated insulation voltage          | 400 V EN/IEC 60947                                                           |
| [Uimp] rated impulse withstand voltage | 3.6 kV IEC 61000-4-5                                                         |
| Contacts material                      | Silver alloy (AgNi)                                                          |
| [Ie] rated operational current         | 4 A AC-1/DC-1) NC IEC<br>8 A AC-1/DC-1) NO IEC                               |
| Minimum switching current              | 10 mA                                                                        |
| Maximum switching voltage              | 300 V DC IEC                                                                 |
| Minimum switching voltage              | 12 V                                                                         |
| Maximum switching capacity             | 2000 VA AC<br>224 W DC                                                       |
| Resistive rated load                   | 8 A 250 V AC<br>8 A 28 V DC                                                  |
| Minimum switching capacity             | 120 mW 10 mA, 12 V                                                           |
| Operating rate                         | <= 600 cycles/hour under load<br><= 18000 cycles/hour no-load                |
| Mechanical durability                  | 5000000 cycles                                                               |
| Electrical durability                  | 100000 Cycles, 8 A at 250 V, AC-1 NO<br>100000 cycles, 4 A at 250 V, AC-1 NC |
| Operating time                         | 20 ms operating<br>20 ms reset                                               |
| Average coil consumption               | 0.75 VA AC                                                                   |
| Drop-out voltage threshold             | >= 0.15 Uc AC                                                                |
| Safety reliability data                | B10d = 100000                                                                |
| Protection category                    | RT I                                                                         |
| Test levels                            | Level A                                                                      |
| Operating position                     | Any position                                                                 |
| Torque Value                           | 7.08 Lbf.in (0.8 N.m)<br>7.0 lbf.in (0.79 N.m)                               |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

|                               |                                                                                                                                                                                                                                                                                                                                                                  |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Connections - terminals       | Connector, 1 x 0.25...1 x 2.5 mm <sup>2</sup> AWG 22...AWG 14) flexible with cable end<br>Connector, 2 x 0.25...2 x 1 mm <sup>2</sup> AWG 22...AWG 17) flexible with cable end<br>Connector, 1 x 0.5...1 x 2.5 mm <sup>2</sup> AWG 20...AWG 14) solid without cable end<br>Connector, 2 x 0.5...2 x 1.5 mm <sup>2</sup> AWG 20...AWG 16) solid without cable end |
| Net Weight                    | 0.13 lb(US) (0.057 kg)                                                                                                                                                                                                                                                                                                                                           |
| Sale per indivisible quantity | 30                                                                                                                                                                                                                                                                                                                                                               |
| Device presentation           | Complete product                                                                                                                                                                                                                                                                                                                                                 |

## Environment

|                                       |                                                                                             |
|---------------------------------------|---------------------------------------------------------------------------------------------|
| Dielectric strength                   | 1000 V AC between contacts<br>2500 V AC between poles<br>5000 V AC between coil and contact |
| Standards                             | EN/IEC 61810-1<br>CSA C22.2 No 14<br>UL 508<br>IEC 61984                                    |
| Product Certifications                | CE<br>UL<br>CSA<br>EAC                                                                      |
| Ambient Air Temperature for Storage   | -40...185 °F (-40...85 °C)                                                                  |
| Vibration resistance                  | +/- 1 mm 10...55 Hz)EN/IEC 60068-2-6                                                        |
| IP degree of protection               | IP20 conforming to EN/IEC 60529                                                             |
| Shock resistance                      | 10 gn 11 ms) not operating EN/IEC 60068-2-27<br>5 gn 11 ms) in operation EN/IEC 60068-2-27  |
| Ambient air temperature for operation | -40...158 °F (-40...70 °C) AC)                                                              |

## Ordering and shipping details

|                       |                             |
|-----------------------|-----------------------------|
| Category              | 21127-ZELIO ICE CUBE RELAYS |
| Discount Schedule     | CP2                         |
| GTIN                  | 3606489562786               |
| Nbr. of units in pkg. | 1                           |
| Package weight(Lbs)   | 19.40 oz (550.0 g)          |
| Returnability         | No                          |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Package 1 Height             | 0.63 in (1.6 cm)        |
| Package 1 width              | 2.56 in (6.5 cm)        |
| Package 1 Length             | 3.35 in (8.5 cm)        |
| Unit Type of Package 2       | S03                     |
| Number of Units in Package 2 | 180                     |
| Package 2 Weight             | 219.36 lb(US) (99.5 kg) |
| Package 2 Height             | 11.81 in (30 cm)        |
| Package 2 width              | 11.81 in (30 cm)        |
| Package 2 Length             | 15.75 in (40 cm)        |
| Unit Type of Package 3       | BB1                     |
| Number of Units in Package 3 | 30                      |
| Package 3 Weight             | 36.60 lb(US) (16.6 kg)  |
| Package 3 Height             | 7.48 in (19 cm)         |
| Package 3 width              | 3.54 in (9 cm)          |
| Package 3 Length             | 10.63 in (27 cm)        |


## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                         |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                                                                                                 |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                          |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                                                                                           |


## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 Months |
|----------|-----------|

Dimensions



## Wiring Diagram




NOTE: For DC input, A1 have to be +, otherwise it would short circuit from protection module

## Electrical Durability of Contacts

Durability (Inductive Load) = Durability (Resistive Load) x Reduction Coefficient.

Resistive AC Load



(y) Durability (Number of operating cycles)


(x) Switching capacity (kVA)

A : RSB2A080●●

B : RSB1A160●●


C : RSB1A120●●

## Reduction Coefficient for Inductive AC Load (Depending on Power Factor $\cos \phi$ )



(y) Reduction coefficient (A)

## Maximum Switching Capacity on Resistive DC Load



(y) Current DC

(x) Voltage DC

A : RSB2A080●●

B : RSB1A160●●

C : RSB1A120●●

NOTE: These are typical curves, actual durability depends on load, environment, duty cycle, etc.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RSB2A080M7PV](#)