

Product data sheet

Characteristics

SC606AHV0

Hyde Park, Ultrasonic sensor, analog, voltage (V), 18 mm barrel, 15-24 V DC



Main

| | |
|-------------------------------|--|
| Range of Product | Hyde Park |
| Sensor Type | Ultrasonic sensor |
| Series name | Superprox + |
| Device short name | SC606 |
| Sensor design | Cylindrical M18 |
| [Sn] nominal sensing distance | 12.00 in (304.8 mm) |
| Type of sensing window | Configurable |
| Material | Plastic |
| Enclosure Material | ULTEM |
| Front material | Silicone rubber |
| Type of output signal | Analog |
| ISO thread | M18 x 1 |
| Wiring Technique | 4-wire |
| [Us] rated supply voltage | 15...24 V DC overload and short-circuit protection |
| Supply voltage limits | 13...28 V DC |
| Analogue output range | 0...10 V configurable |
| Electrical connection | Cable, 9.84 ft (3 m) |
| Product Specific Application | Analog output |

Complementary

| | |
|---------------------------------|--|
| Blind zone | 0.75 in (19 mm) |
| Transmission frequency | 500 kHz |
| Beam angle | 10 ° |
| Minimum size of detected object | Cylinder diameter 1.59 mm - up to 76.2 mm sensing distance |
| Current Consumption | 50 mA |
| Maximum switching current | 100 mA reverse polarity protection |
| Height | 0.71 in (18 mm) |
| Width | 0.71 in (18 mm) |
| Depth | 0.71 in (18 mm) |
| Length | 2.55 in (64.77 mm) |
| Net Weight | 0.40 lb(US) (0.18 kg) |

Environment

| | |
|---------------------------------------|--|
| Product Certifications | UL |
| Marking | CE |
| NEMA degree of protection | NEMA 4X indoor use only) |
| IP degree of protection | IP67 |
| Ambient air temperature for operation | 32...140 °F (0...60 °C) |
| Ambient Air Temperature for Storage | -40...212 °F (-40...100 °C) |
| Relative humidity | 100 % without condensation |
| Vibration resistance | +/-1 mm 10...55 Hz) IEC 60068-2-6 |
| Shock resistance | 30 gn in all 3 axes 11 ms IEC 60068-2-27 |
| Resistance to electromagnetic fields | 9.14 V/m (10 V/m) level 3 IEC 61000-4-3 |
| Resistance to fast transients | 1 kV level 3 IEC 61000-4-4 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 22490 - SENSORS-ULTRASONIC (XX5,6) |
| Discount Schedule | DS2 |
| GTIN | 03389119086462 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.12 lb(US) (0.05 kg) |
| Returnability | No |
| Country of origin | US |

Offer Sustainability

| | |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SC606AHV0](#)