



## Overview

Lead time	Usually in Stock
-----------	------------------

## Main

Main Input Voltage	200 V 208 V 230 V 3 phase
Main Output Voltage	120 V 200 V 208 V 230 V
Other Output Voltage	220 V 240 V
Output connector type	Hard Wire 3-wire (H N + E) 1 Hard Wire 3-wire (2PH + G) 1 Hard Wire 4-wire (2PH+N+G) 1
Number of rack unit	4U
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets User Manual

## Physical

Color	Black
Height	7.01 in (17.8 cm)
Width	17.01 in (43.2 cm)
Depth	25.98 in (66 cm)
Net Weight	47.09 lb(US) (21.36 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted

## Input

Input Frequency	50/60 Hz
Number of input connectors	1 Hard Wire 3-wire (H N + E) 1 Hard Wire 3-wire (2PH + G) 1 Hard Wire 4-wire (2PH+N+G) 1 Hard Wire 5-wire (3PH + N + G)
Acceptable Input Voltage	200...240 V
Max line current	100 A
Input current limits	100 A
Load Capacity	20000 VA
Load Power Factor Range	0...1

## Output

Maximum Total Current Draw per Phase	100 A
Protection Type	Circuit breaker
Efficiency	99 %

## Conformance

Product Certifications	CSA GOST
Standards	EN 60950 IEC 60950 IEC 60950 UL 1778

## Environmental

Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Relative Humidity	0...95 %
Operating altitude	0...15000 ft
Ambient Air Temperature for Storage	-40...149 °F (-40...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304212645
Package weight(Lbs)	69.14 lb(US) (31.36 kg)

## Packing Units

Package 1 Height	12.01 in (30.5 cm)
Package 1 width	24.02 in (61 cm)
Package 1 Length	39.02 in (99.1 cm)

## Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
-------------------	---

## Contractual warranty

Warranty	2 years (parts only)
----------	----------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SBP16KP](#)