



Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------



Main

Main Input Voltage	120 V
Other Input Voltage	110 V 125 V
Main Output Voltage	120 V
Other Output Voltage	110 V 125 V
Kw Rating	600 W
Rated power in VA	1000 VA
Plug standard	NEMA 5-15P
Nb of power socket outlets	6 NEMA 5-15R
Number of rack unit	2U
Cable length	8 ft (2.44 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	Documentation CD Installation guide Rack Mounting brackets USB cable

General

Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Cloud-enabled monitoring
Redundant	No

Physical

Color	Black
Height	3.39 in (8.6 cm)
Width	17.01 in (43.2 cm)
Depth	15.98 in (40.6 cm)
Net Weight	45.24 lb(US) (20.52 kg)
Mounting Location	Front
Mounting preference	Lower

Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	85...136 V adjustable 93...130 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	1000 VA
Max Configurable Power (Watts)	600 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CULus ENERGY STAR V2.0 (USA)
Equipment protection policy	Lifetime : \$150000
Standards	CSA C22.2 No. 107.1 FCC Part 15 class A ICES-003 UL 1778

Environmental

Acoustic level	41 dBA
Heat dissipation	175 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Life	4...6 year(s)
Battery power in VAh	216 VAh runtime
Battery Charge Power (Watts)	72 W rated

Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multi-function LCD status and control console
Free slots	0

Surge Protection and Filtering

Surge energy rating	680 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	731304322733
Package weight(Lbs)	45.66 lb(US) (20.71 kg)

Packing Units

Package 1 Height	9.25 in (23.5 cm)
Package 1 width	21.06 in (53.5 cm)
Package 1 Length	22.44 in (57 cm)
Number of Units in Package 3	16

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMC1000-2UC](#)