



Overview

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

General

Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack mounting support rails Smart UPS signalling RS-232 cable USB cable
Number of tare power	98 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Cable length	3.66 M
Number of rack unit	2U
Colour	Black
Depth	68.3 Cm
Height	8.6 Cm
Mounting location	Front
Mounting preference	Lower
Product weight	44.28 Kg
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Width	48 Cm

Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	NEMA L5-30P
Input voltage limits	75...154 V adjustable 82...144 V
Number of cables	1
Input voltage	120 V

Output

Rated power in W	2700 W
Maximum configurable power in W	2700 W
Harmonic distortion	Less than 5 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
UPS type	Line interactive
Wave type	Sine wave
Nb of power socket outlets	6 NEMA 5-15R 2 NEMA 5-20R
Output voltage	120 V
Maximum configurable power in VA	2880 VA
Rated power in VA	2880 VA
Transfer time	4 ms typical : 8 ms maximum

Conformance

Product certifications	CSA
Standards	FCC part 15 class A UL 1778
Equipment protection policy	Lifetime : \$150000

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 M
Acoustic level	55 dBA
Heat dissipation	348 Btu/H

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Liquid value	0
Battery charger power	188 W rated
Battery power in VAH	566 VAh runtime
Battery life	3...5 Year(S)
Extended runtime	0

Communications & Management

Free slots	1
Control panel	LED status display with on line : on battery : replace battery and overload indicators Multifunction LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm

Surge Protection and Filtering

Surge energy rate	459 J
-------------------	-------

Packing Units

Package 1 Weight	51.7 Kg
Package 1 Height	25.4 Cm
Package 1 width	60 Cm
Package 1 Length	98 Cm
Number of Units in Package 3	8

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and-lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMT3000R2X145](#)