

SMX3000HVT

APC Smart-UPS X 3000VA Short Depth Tower/Rack Convertible LCD 208V



Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable run-time. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

General

Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable User manual USB cable Rack mounting brackets
Additional specification	Extended run
Number of power module	2400
Number of tare power	41 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Number of rack unit	4U
Colour	Black
Depth	48.3 Cm
Height	43.2 Cm
Mounting location	Front
Mounting preference	Lower
Product weight	38.64 Kg
Mounting mode	Rack-mounted
Two post mountable	1
USB compatible	Yes
Width	17.8 Cm

Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	NEMA L6-20P
Input voltage limits	141...255 V 160...280 V
Inputvolt_other	220 V 230 V 240 V
Number of cables	1
Input voltage	208 V

Output

Rated power in W	2700 W
Maximum configurable power in W	2700 W
Harmonic distortion	Less than 5 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Output voltage	220 V 230 V 240 V
Crest factor	3 : 1
UPS type	Line interactive
Wave type	Sine wave
Nb of power socket outlets	2 NEMA L6-20R 4 IEC 320 C13 3 IEC Jumpers 2 IEC 320 C19
Output voltage	208 V
Maximum configurable power in VA	3000 VA
Rated power in VA	3000 VA
Transfer time	2-4 ms 4 ms typical : 8 ms maximum

Conformance

Product certifications	C-Tick CE CSA GOST IRAM VDE
Standards	EN 50091-1 EN 50091-2 EN 60950 FCC part 15 class A UL 1778

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 M
Acoustic level	55 dBA
Heat dissipation	184 Btu/H

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Liquid value	0
Battery charger power	245 W rated
Battery power in VAh	738 VAh runtime
Battery life	3...5 Year(S)
Battery option	SMX120BP 1 2214 VAh SMX120BP 2 3690 VAh SMX120BP 3 5166 VAh SMX120BP 4 6642 VAh SMX120BP 6 9594 VAh SMX120BP 8 12546 VAh SMX120BP 10 15498 VAh
Extended runtime	1

Communications & Management

Free slots	1
Control panel	LED status display with on line : on battery : replace battery and overload indicators Multifunction LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency power off	Yes






Surge Protection and Filtering

Surge energy rate	645 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Package 1 Weight	47.73 Kg
Package 1 Height	33 Cm
Package 1 width	58.6 Cm
Package 1 Length	63.3 Cm
Number of Units in Package 3	6
Package 3 Weight	388.69 Kg
Package 3 Height	110.49 Cm
Package 3 width	121.92 Cm
Package 3 Length	78.74 Cm
Pallet unit layers	2
Pallet layers	4

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and-lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go-to www.P65Warnings.ca.gov
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--

Product Life Status :	Commercialised
-----------------------	----------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMX3000HVT](#)