



## Main

|                               |                                                    |
|-------------------------------|----------------------------------------------------|
| Range of Product              | Hyde Park                                          |
| Sensor Type                   | Ultrasonic sensor                                  |
| Series name                   | Superprox 300                                      |
| Device short name             | SM300                                              |
| Sensor design                 | Flat form miniature                                |
| [Sn] nominal sensing distance | 3.12 in (79.37 mm)                                 |
| Type of sensing window        | Fixed                                              |
| Material                      | Plastic                                            |
| Enclosure Material            | ULTEM                                              |
| Front material                | Glass epoxy                                        |
| Type of output signal         | Discrete                                           |
| Discrete output function      | 1 NO                                               |
| Wiring Technique              | 4-wire                                             |
| [Us] rated supply voltage     | 12...24 V DC overload and short-circuit protection |
| Supply voltage limits         | 10...28 V DC                                       |
| Discrete output type          | PNP/NPN                                            |
| Electrical connection         | Cable, 9.84 ft (3 m)                               |
| Product Specific Application  | Discrete proximity                                 |

## Complementary

|                                 |                                                        |
|---------------------------------|--------------------------------------------------------|
| [Sd] sensing range              | 2.61...3.12 in (66.37...79.37 mm)                      |
| Maximum differential travel     | 0.03 in (0.7 mm)                                       |
| Blind zone                      | 0.25 in (6.4 mm)                                       |
| Transmission frequency          | 500 kHz                                                |
| Repeat accuracy                 | 0.7 %                                                  |
| Beam angle                      | 8 °                                                    |
| Minimum size of detected object | Cylinder diameter 2.5 mm - up to 1 mm sensing distance |
| Current Consumption             | 25 mA                                                  |
| Maximum switching current       | 100 mA reverse polarity protection                     |
| Height                          | 0.30 in (7.62 mm)                                      |
| Width                           | 0.75 in (19.05 mm)                                     |
| Depth                           | 0.30 in (7.62 mm)                                      |
| Length                          | 1.30 in (33.02 mm)                                     |
| Net Weight                      | 0.26 lb(US) (0.12 kg)                                  |

## Environment

|                                       |                                          |
|---------------------------------------|------------------------------------------|
| Product Certifications                | UL                                       |
| Marking                               | CE                                       |
| NEMA degree of protection             | NEMA 4X indoor use only)                 |
| IP degree of protection               | IP67                                     |
| Ambient air temperature for operation | -22...158 °F (-30...70 °C)               |
| Ambient Air Temperature for Storage   | -40...212 °F (-40...100 °C)              |
| Relative humidity                     | 100 % without condensation               |
| Vibration resistance                  | +/-1 mm 10...55 Hz)IEC 60068-2-6         |
| Shock resistance                      | 30 gn in all 3 axes 11 ms IEC 60068-2-27 |

|                                      |                                         |
|--------------------------------------|-----------------------------------------|
| Resistance to electromagnetic fields | 9.14 V/m (10 V/m) level 3 IEC 61000-4-3 |
| Resistance to fast transients        | 1 kV level 3 IEC 61000-4-4              |

## Ordering and shipping details

|                       |                                    |
|-----------------------|------------------------------------|
| Category              | 22490 - SENSORS-ULTRASONIC (XX5,6) |
| Discount Schedule     | DS2                                |
| GTIN                  | 03389119088220                     |
| Nbr. of units in pkg. | 1                                  |
| Package weight(Lbs)   | 0.26 lb(US) (0.12 kg)              |
| Returnability         | No                                 |
| Country of origin     | US                                 |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                               |
| RoHS exemption information |  Yes                                                                                                                                                                                                                                                                                             |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SM300AA0400FP](#)