

Product data sheet

Characteristics

SUM1500RMXL2U

APC Smart-UPS XL Modular 1500VA 120V
Rackmount/Tower (Not for sale in CO, VT or
WA)



Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually Ships within 4 Weeks

Main

Kw Rating	1425 W
Rated power in VA	1440 VA
Nb of power socket outlets	8 NEMA 5-15R
Main Output Voltage	120 V
Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Number of rack unit	2U
Cable length	10 ft (3.05 m)
Number of cables	1

General

Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Network card pre-installed
Redundant	No
Provided equipment	CD with software Installation guide Rack Mounting brackets Rack Mounting support rails Smart UPS signalling RS-232 cable User Manual USB cable Web/SNMP Management Card

Physical

Mounting Location	Front
Mounting Mode	Rack-mounted
Mounting preference	Lower
Depth	26.69 in (67.8 cm)
Height	3.39 in (8.6 cm)
Net Weight	103.22 lb(US) (46.82 kg)
Width	17.01 in (43.2 cm)
Two post mountable	0

USB compatible	No
Color	Black

Input

Efficiency at full load	75...154 V adjustable 82...147 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Bypass type	Internal Bypass (Automatic and Manual)
Maximum configurable power in VA	1440 VA
Max Configurable Power (Watts)	1425 W
Maximum output current	24 A
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	BSMI CSA NOM VCCI Class A
Equipment protection policy	Lifetime : \$150000
Standards	FCC Part 15 class A UL 1778

Environmental

Acoustic level	55 dBA
Heat dissipation	300 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	23...131 °F (-5...55 °C)
Storage altitude	0...30000 ft (0.00...9144.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Type	VRLA
Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	3...5 year(s)
Battery power in VAH	600 VAh runtime
Battery Charge Power (Watts)	199 W rated
Battery option	SUM48RMXLBP2U 1 1440 VAh SUM48RMXLBP2U 2 2400 VAh SUM48RMXLBP2U 3 3360 VAh SUM48RMXLBP2U 4 4320 VAh SUM48RMXLBP2U 5 5280 VAh SUM48RMXLBP2U 6 6240 VAh SUM48RMXLBP2U 8 8160 VAh SUM48RMXLBP2U 10 10080 VAh

Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : Overload and Bypass Indicators
Emergency Power Off (EPO)	Optional
Free slots	0
Pre-Installed SmartSlot™ Cards	Network management card 2 with environmental monitoring

Surge Protection and Filtering

Surge energy rating	540 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	00731304224549
Package weight(Lbs)	125.27 lb(US) (56.82 kg)

Packing Units

Package 1 Height	9.84 in (25 cm)
Package 1 width	23.46 in (59.6 cm)
Package 1 Length	38.58 in (98 cm)
Number of Units in Package 3	8

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	<input checked="" type="checkbox"/> REACH Declaration
EU RoHS Directive	Compliant <input checked="" type="checkbox"/> EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	<input checked="" type="checkbox"/> Yes
Environmental Disclosure	<input checked="" type="checkbox"/> Product Environmental Profile
Circularity Profile	<input checked="" type="checkbox"/> End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SUM1500RMXL2U](#)