

Product data sheet

Characteristics

TSXCANCADD03

CANopen cordset - molded female SUB-D9 connectors - standard - IP20 - 0.3 m

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	CANopen
Bus type	CANopen
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part destination	CANopen bus
Cable length	0.98 Ft (0.3 m)

Complementary

Electrical connection	2 female connectors SUB-D 9
Marking	CE
Product Weight	0.20 Lb(US) (0.091 kg)

Environment

IP degree of protection	IP20
-------------------------	------

Ordering and shipping details

Category	22531 - PLCS, TWIDO, TWD
Discount Schedule	PC12
GTIN	3595863860153
Nbr. of units in pkg.	1
Package weight(Lbs)	3.21 Oz (91 g)
Returnability	No
Country of origin	PT

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.39 In (1 cm)
Package 1 width	5.91 In (15 cm)
Package 1 Length	7.87 In (20 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric:

TSXCANCADD03