



Main

Product or Component Type	Separate inductive head
Range of Product	Telemecanique Radio frequency identification XG

Complementary

Enclosure Material	PPS
Fixing Mode	By screws
Depth	0.67 in (17 mm)
Detector design	Rectangular
Electrical Connection	Connector
Height	1.57 in (40 mm)
[Sn] nominal sensing distance	2.36 in (60 mm)
Outer dimension	60 x 40 x 17 mm
Net Weight	0.13 lb(US) (0.058 kg)
Shape of legend	Rectangular
Tag type	Read/write code
Width	2.36 in (60 mm)
Working sensing distance	1.89 in (48 mm)

Environment

Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
IP Degree of Protection	IP65
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)

Ordering and shipping details

Category	22491-SENS,IDENTIFICATION DEVICE (XGK)
Discount Schedule	DS2
GTIN	03389118325418
Package weight(Lbs)	0.44 lb(US) (0.198 kg)
Returnability	No
Country of origin	FR

Packing Units

Package 1 Height	0.550 dm
Package 1 width	1.500 dm
Package 1 Length	0.900 dm

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[XGSP1587969](#)