



Main

Range of product	Harmony XVS
Product or component type	Electronic alarm
Device short name	XVS

Complementary

Colour	White
Material	PC (polycarbonate): terminal cover PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene): body
Product weight	0.4 Kg
Marking	CE
Overvoltage category	Class II conforming to EN/IEC 61140
Mounting support	96 mm DIN rail
[Us] rated supply voltage	12...24 V DC
[Uimp] rated impulse withstand voltage	0.8 KV
Current consumption	250 mA at 12 V 292 mA at 12 V 292 mA at 24 V 354 mA at 24 V
Clamping connection capacity	<= 1 x 1.5 mm ²
Width	96 Mm
Height	96 Mm
Depth	58.1 Mm

Environment

Discrete output type	NPN
Signalling type	16 tones alarm
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-20...50 °C
IP degree of protection	Panel mounted: IP54 conforming to EN/IEC 60529
Noise level	0...96 DB (continuous or intermittent tone) at 1 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	534 G
Package 1 Height	13.5 Cm
Package 1 width	14.1 Cm
Package 1 Length	14.1 Cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and-lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVS96BMWN](#)