

SMT750I

APC Smart-UPS, Line Interactive, 750VA,
Tower, 230V, 6x IEC C13 outlets, SmartSlot,
AVR, LCD



Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable run-time. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually Ships within 2 Weeks

Main

Input voltage	230 V
Input voltage	220 V 240 V
Output voltage	230 V
Output voltage	220 V 240 V
Rated power in W	500 W
Rated power in VA	750 VA
Plug standard	IEC 320 C14
Nb of power socket outlets	6 IEC 320 C13 2 IEC Jumpers
Cable length	1.83 M
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable USB cable

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Physical

Colour	Black
Height	15.75 Cm
Width	13.8 Cm
Depth	35.81 Cm
Net weight	13.18 Kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Input voltage limits	151...302 V adjustable 160...280 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5 % at full load
Maximum configurable power in VA	750 VA
Maximum configurable power in W	500 W
Transfer time	4 ms typical : 8 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	47...53 Hz for 50 Hz nominal sync to mains 57...63 Hz for 60 Hz nominal sync to mains

Conformance

Product certifications	CE EAC RCM VDE
Standards	EN/IEC 62040-1 EN/IEC 62040-2

Environmental

Acoustic level	40 dBA
Heat dissipation	90 Btu/H
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Battery life	3...5 Year(S)
Battery power in VAh	146 VAh runtime
Battery charger power	49 W rated

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multifunction LCD status and control console
Emergency power off	Optional
Free slots	1






Surge Protection and Filtering

Surge energy rate	540 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Package 1 Weight	14.23 Kg
Package 1 Height	30.1 Cm
Package 1 width	27.8 Cm
Package 1 Length	49.9 Cm
SCC14	731304269069
Number of Units in Package 3	24

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Product Life Status : **Commercialised**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMT750I](#)