

Product data sheet

Characteristics

VM18NPI3000Q

Hyde Park, Ultrasonic sensor, dual level, pump in latch, 18 mm barrel, 12 24 V DC



Main

Range of Product	Hyde Park
Sensor Type	Ultrasonic sensor
Series name	Virtu VM18
Device short name	VM18
Sensor design	Cylindrical M18
[Sn] nominal sensing distance	20.00 in (508 mm)
Type of sensing window	Adjustable
Material	Plastic
Enclosure Material	PBT
Front material	Glass epoxy
Type of output signal	Discrete
Discrete output function	1 NO
ISO thread	M18 x 1
Wiring Technique	4-wire
[Us] rated supply voltage	12...24 V DC overload and short-circuit protection
Supply voltage limits	10...28 V DC
Discrete output type	NPN
Electrical connection	1 male connector M12 4 pins
Product Specific Application	Dual-level - pump-in latch

Complementary

[Sd] sensing range	2.00...20.00 in (50.8...508 mm)
Blind zone	2.01 in (51 mm)
Transmission frequency	300 kHz
Repeat accuracy	1.27 %
Beam angle	5 °
Minimum size of detected object	Cylinder diameter 2.5 mm - up to 200 mm sensing distance
Status LED	Output not active 1 LED green)
Current Consumption	40 mA
Maximum switching current	100 mA reverse polarity protection
Height	0.71 in (18 mm)
Width	0.71 in (18 mm)
Depth	0.71 in (18 mm)
Length	3.06 in (77.62 mm)
Net Weight	0.07 lb(US) (0.033 kg)

Environment

Standards	EN 60947
Product Certifications	UL
Marking	CE
NEMA degree of protection	NEMA 4X indoor use only)
IP degree of protection	IP67
Ambient air temperature for operation	-22...158 °F (-30...70 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Relative humidity	100 % without condensation

Vibration resistance	+/-1 mm 10...55 Hz)IEC 60068-2-6
Shock resistance	30 gn in all 3 axes 11 ms IEC 60068-2-27
Resistance to electromagnetic fields	9.14 V/m (10 V/m) level 3 IEC 61000-4-3
Resistance to fast transients	1 kV level 3 IEC 61000-4-4

Ordering and shipping details

Category	22490 - SENSORS-ULTRASONIC (XX5,6)
Discount Schedule	DS2
GTIN	03389119062565
Nbr. of units in pkg.	1
Package weight(Lbs)	0.14 lb(US) (0.06 kg)
Returnability	No
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[VM18NPI3000Q](#)