



Main

Range	TeSys
Device short name	LU9MR
Product or Component Type	Pre-wired connector

Complementary

Net Weight	0.08 lb(US) (0.035 kg)
Tightening torque	Control circuit 7.08...10.62 lbf.in (0.8...1.2 N.m) flat 0.20 in (5 mm) Control circuit 7.08...10.62 lbf.in (0.8...1.2 N.m) Philips No 2 0.20 in (5 mm) Power circuit 16.82...22.13 lbf.in (1.9...2.5 N.m) flat 0.24 in (6 mm) Power circuit 16.82...22.13 lbf.in (1.9...2.5 N.m) Philips No 2 0.24 in (6 mm) Power circuit 16.82...22.13 lbf.in (1.9...2.5 N.m) pozidriv No 2 0.24 in (6 mm)

Ordering and shipping details

Category	22399-TESYS U, ACCESSORIES
Discount Schedule	I11
GTIN	3389110367614
Nbr. of units in pkg.	1
Package weight(Lbs)	2.10 oz (59.667 g)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.97 in (5 cm)
Package 1 width	2.36 in (6 cm)
Package 1 Length	2.95 in (7.5 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Weight	7.12 lb(US) (3.23 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LU9MR1C](#)