



## Overview

Presentation	Highly efficient, easy-to-deploy 50kW, 480V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. This UPS is for up to 4 smart modular high capacity battery strings, but is supplied without batteries, so you can easily customize the battery runtime. Includes 5x8 start-up service.
Lead time	Usually Ships within 2 Weeks

## Main

Main Input Voltage	3 phase
Main Output Voltage	480 V 3 phase
Kw Rating	50 kW
Rated power in VA	50 kVA
Battery Type	Internal modular battery VRLA
Provided equipment	Dust filter Installation manual Integrated network management Start-Up Service EcoStruxure Ready

## General

Bypass Voltage Tolerance	+/- 10 %
Redundant	No

## Physical

Color	White
Height	58.46 in (148.5 cm)
Width	20.51 in (52.1 cm)
Depth	33.35 in (84.7 cm)
Net Weight	440.92 lb(US) (200 kg)
USB compatible	No

## Input

Input Frequency	40 - 70 Hz
Efficiency at full load	408...552 V 480 V
Maximum Input Current per Phase	74 A
Maximum Short Circuit Withstand (Icw)	65 kA
Input Total Harmonic Distortion	Less than 3% for full load
Load power factor	From 0.7 leading to 0.7 lagging without any derating
Input Power Factor at Full Load	0.99

## Output

Max Configurable Power (Watts)	50 kW
Harmonic distortion	Less than 5%
Output Frequency (sync to mains)	50 Hz sync to mains 60 Hz sync to mains
Crest factor	2.5
Waveform Type	Sine wave
Output voltage tolerance	+/-1% after 50ms
Output Voltage THD	< 1% linear load and < 5% non-linear load
Overload Operation	10 minutes @ 125% and 60 seconds @ 150%
Bypass type	Built-in Static Bypass
Maximum configurable power in VA	50 kVA

## Conformance

Product Certifications	ENERGY STAR V2.0 (USA)
Standards	CSA C22.2 No 107.3 FCC Part 15 class A IEC 62040-1-1 IEC 62040-2 IEC 62040-3 UL 1778 5th edition OSHDP

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...3300 ft
Ambient Air Temperature for Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	Non-condensing 10...80 %
Storage altitude	0...10000 ft (0.00...3048.00 m)
Acoustic level	61 dBA
Heat dissipation	5210 Btu/h
IP degree of protection	IP20

## Batteries & Runtime

Battery Voltage	480V
End of Discharge Battery Voltage	384 V DC
End of Discharge Maximum Battery Current	135 A
Battery power in VAh	0 VAh runtime
Extendable Run Time	0

## Communications & Management

Free slots	1
Control panel	Touch Screen LCD User Interface
Audible Alarm	Audible and visible alarms prioritized by severity








## Ordering and shipping details

GTIN	731304409939
Package weight(Lbs)	440.92 lb(US) (200 kg)

## Packing Units

Package 1 Height	66.14 in (168 cm)
Package 1 width	25.20 in (64 cm)
Package 1 Length	38.98 in (99 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
ENERGY STAR®	 <a href="#">ENERGY STAR UPS V2.0 (USA)</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GVSUPS50K0B4GS](#)