

SRT3000XLAUS

APC Smart-UPS On-Line, 3kVA, Rack/Tower, 120V, 8x 5-20R+1x L5-30R NEMA outlets, SmartSlot, Extended runtime, W/O rail kit, TAA



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	2700 W
Rated power in VA	3000 VA
Plug standard	NEMA L5-30P
Nb of power socket outlets	8 NEMA 5-20R 1 NEMA L5-30R
Cable length	10 ft (3.05 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Installation guide Removable support feet USB cable Warranty card

General

Product web sub-family	TAA compliance
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Color	Black
Height	17.01 in (43.2 cm)
Width	3.35 in (8.5 cm)
Depth	25.00 in (63.5 cm)
Net Weight	69.00 lb(US) (31.3 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Not rack-mountable

Two post mountable	0
USB compatible	Yes
Mounting position	Vertical

Input

Input Frequency	40 - 70 Hz auto-sensing
-----------------	-------------------------

Output

Max Configurable Power (Watts)	2700 W
Harmonic distortion	Less than 2%
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Crest factor	3 : 1
Topology	Double Conversion Online
Waveform Type	Sine wave
Bypass type	Internal Bypass (Automatic and Manual)
Maximum configurable power in VA	3000 VA

Conformance

Product Certifications	TAA compliance ENERGY STAR V2.0 (USA)
Standards	CSA C22.2 No.107.3-05 FCC Part 15 class A UL 1778

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	Non-condensing 0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	55 dBA
Heat dissipation	805 Btu/h
IP degree of protection	IP20

Batteries & Runtime

Included Battery Modules	1
Typical recharge time	3 h
RBC Quantity	1
Battery Charge Power (Watts)	151 W rated
Battery power in VAh	454 VAh runtime
Battery Life	3...5 year(s)
Battery option	SRT96BP 1 1362 VAh SRT96BP 2 2270 VAh SRT96BP 3 3178 VAh SRT96BP 4 4086 VAh SRT96BP 5 4994 VAh SRT96BP 6 5902 VAh SRT96BP 8 7718 VAh SRT96BP 10 9534 VAh
Extendable Run Time	1

Communications & Management

Free slots	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	340 J
---------------------	-------







Ordering and shipping details

GTIN	731304340478
Package weight(Lbs)	81.00 lb(US) (36.74 kg)

Packing Units

Package 1 Height	9.69 in (24.6 cm)
Package 1 width	23.58 in (59.9 cm)
Package 1 Length	34.29 in (87.1 cm)
Number of Units in Package 3	6

Offer Sustainability

Sustainable offer status	Green Premium product
ENERGY STAR®	 ENERGY STAR UPS V2.0 (USA)
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SRT3000XLAUS](#)