

Main

Range of product	OsiSense XX
Sensor type	Ultrasonic sensor
Sensor name	XX9
Material	Stainless steel
Sensor design	Ø 30 mm
Product specific application	For 2 levels monitoring
Type of output signal	Dual-level - dual setpoint
Wiring technique	4 wires
[Us] rated supply voltage	12...24 V DC with reverse polarity protection
Discrete output function	1 NO
Discrete output type	PNP
Electrical connection	1 male connector M12 4 pins
[Sd] sensing range	0.17...0.33 ft (0.051...0.1 m)
Beam angle	10 °
IP degree of protection	IP67 conforming to IEC 60529

Complementary

Enclosure material	Stainless Steel
Front material	Silicone
ISO thread	M30 x 1.5
Supply voltage limits	10...28 V DC
[Sn] nominal sensing distance	3.28 ft (1 m)
Type of sensing window	Adjustable
[Sa] assured operating distance	0.17...3.25 ft (0.051...0.991 m) teach mode)
Maximum differential travel	0.10 in (2.5 mm)
Blind zone	2.01 in (51 mm)
Transmission frequency	200 kHz
Repeat accuracy	0.9 %
Deviation angle from 90° of object to be detected	-10...10 °
Minimum size of detected object	Cylinder diameter 1.6 mm - up to 635 mm sensing distance
Status LED	Output state 2 LEDs green/red (flashing)) Setting-up assistance 2 LEDs green/red (flashing)) Distance indication 2 LEDs yellow)
Current consumption	100 mA
Maximum switching current	100 mA overload and short-circuit protection
Maximum delay first up	1000 ms
Maximum delay response	150 ms
Maximum delay recovery	1000 ms
Marking	CE
Height	1.18 in (30 mm)
Maximum Width	1.18 in (30 mm)
Depth	1.18 in (30 mm)
Length	3.78 in (96 mm)
CAD overall height	3.78 in (95.99 mm)
CAD overall width	1.35 in (34.17 mm)

CAD overall depth	1.35 in (34.17 mm)
Net Weight	0.60 lb(US) (0.27 kg)

## Environment

Standards	IEC 60947-5-2
Product certifications	UL
NEMA degree of protection	NEMA 4X indoor use only)
Ambient air temperature for operation	32...122 °F (0...50 °C)
Ambient air temperature for storage	14...176 °F (-10...80 °C)
Vibration resistance	+/-1 mm 10...55 Hz)IEC 60068-2-6
Shock resistance	30 gn in all 3 axes 11 ms IEC 60068-2-27
Resistance to electrostatic discharge	8 kV level 4 IEC 61000-4-2
Resistance to electromagnetic fields	9.14 V/m (10 V/m) level 3 IEC 61000-4-3
Resistance to fast transients	1 kV level 3 IEC 61000-4-4

## Ordering and shipping details

Category	22490 - SENSORS-ULTRASONIC (XX5,6)
Discount Schedule	DS2
GTIN	03389119130554
Nbr. of units in pkg.	1
Package weight(Lbs)	0.9 lb(US) (0.41 kg)
Returnability	No
Country of origin	US

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

## Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XX930SS1P5M12](#)