

# PNET1GB

APC ProtectNet standalone surge protector for  
10/100/1000 Base-T Ethernet lines



## Overview

Presentation	Protects an Ethernet data port from damaging surges. Compatible with- Power over Ethernet (PoE) and 10/100/1000 Base-T networks.
Lead time	Usually in Stock

## General

Provided equipment	15 cm Network patch cable User manual
--------------------	--

## Physical

Color	Beige
Depth	1.10 In (2.8 cm)
Height	4.09 In (10.4 cm)
Product Weight	0.11 Lb(US) (0.05 kg)
Width	1.85 In (4.7 cm)

## Conformance

Standards	UL 497B
-----------	---------

## Environmental

Ambient Air Temperature for Operation	5...149 °F (-15...65 °C)
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...149 °F (-15...65 °C)
Storage Relative Humidity	0...95 %

### Surge Protection and Filtering

Data Lines Protected (multi-line only)	1-8
NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	0 DB
Peak current	0.25 KA common mode 6.5 KA normal mode
Data line protection	RJ45 10/100/1000 Base-T Ethernet protection

### Ordering and shipping details

GTIN	00731304226734
Package weight(Lbs)	0.24 Lb(US) (0.11 kg)

### Packing Units

Package 1 Height	4.09 In (10.4 cm)
Package 1 width	3.54 In (9 cm)
Package 1 Length	1.14 In (2.9 cm)
SCC14	10731304226731
Number of Units in Package 2	144
Package 2 Weight	46.2 Lb(US) (20.96 kg)
Package 2 Height	17 In (431.80 mm)
Package 2 width	23 In (584.20 mm)
Package 2 Length	21 In (533.40 mm)
Number of Units in Package 3	1152

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	10 years repair or replace
----------	----------------------------

Product Life Status : **Commercialised**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PNET1GB](#)