

# 9007MS02G0054

## LIMIT SWITCH 240VAC 3 AMP MS +OPTIONS

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch
Device short name	9007MS/ML
Sensor design	Miniature
Body type	Fixed
Head type	Plunger head
Material	Metal
Body material	Cast zinc
Number of poles	1

### Complementary

Fixing mode	By the body
Movement of operating head	Linear
Type of operator	Spring return parallel roller plunger steel (-)
Type of approach	Lateral approach 2 directions
Switch actuation	By 30° cam
Contacts type and composition	NC-NO
Switch function	SPDT
Contact form	Form C
Contacts material	Gold flashed contacts
Contact operation	Snap action
Positive opening	Without
Electrical connection	Male connector M12 micro DC type 4 pins bottom
Terminals description ISO n°1	(3-4)NC (1)Gnd (2-4)NO
Maximum force for tripping	80 ozf
[Ie] rated operational current	100 mAat 125 V AC 30 mAat 28 V DC
[Ithe] conventional enclosed thermal current	3 A
[Ui] rated insulation voltage	300 V degree of pollution 3 conforming to CSA C22.2 No 14 300 V degree of pollution 3 conforming to UL 508
Electrical durability	100000 cycles
Mechanical durability	10000000 cycles
Marking	CE CSA UL
Sale per indivisible quantity	1
Height	1.75 in
Width	1.56 in
Depth	0.62 in
Product weight	1.2 lb(US)

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Shock resistance	35 gn (duration = 9 ms) conforming to IEC 60068-2-27
Vibration resistance	10 gn (f = 75...1200 Hz) conforming to IEC 60068-2-6
NEMA degree of protection	NEMA 2 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 6 conforming to Nema type 250 NEMA 6P conforming to Nema type 250 NEMA 1 conforming to Nema type 250
IP degree of protection	IP67 conforming to IEC 60529
Ambient air temperature for operation	-40...220 °F
Ambient air temperature for storage	-40...220 °F
Protective treatment	Epoxy powder coat
Product certifications	CE CSA UL
Standards	LR 25490 Class 32 11 03 E78403

## Ordering and shipping details

Category	22431 - LIMIT SWITCHES,TYPE 9007MS
Discount Schedule	DS1
GTIN	00785901711636
Nbr. of units in pkg.	1
Package weight(Lbs)	1.2
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9007MS02G0054](#)