

SMX3000HVT

APC Smart-UPS X 3000VA Short Depth Tower/Rack Convertible LCD 208V



Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock

Main

Kw Rating	2700 W
Rated power in VA	3000 VA
Nb of power socket outlets	2 NEMA L6-20R 4 IEC 320 C13 3 IEC Jumpers 2 IEC 320 C19
Output voltage	208 V
Other Output Voltages	220 V 230 V 240 V
Nominal Input Voltage	208 V
Plug standard	NEMA L6-20P
Number of rack unit	4U
Number of cables	1

General

Number of power module	2400
Number of power module filled slots	0
Number of power module free slots	0
Number of tare power	41 W
Product web sub-family	Extended run
Redundant	No
Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable User Manual USB cable Rack Mounting brackets

Physical

Mounting Location	Front
Mounting Mode	Rack-mounted
Mounting preference	Lower
Depth	19.02 in (48.3 cm)
Height	17.01 in (43.2 cm)

Product Weight	85.19 lb(US) (38.64 kg)
Width	7.01 in (17.8 cm)
Two post mountable	1
USB compatible	Yes
Color	Black

Input

Other Input Voltages	220 V 230 V 240 V
Efficiency at full load	141...255 V 160...280 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Crest factor	3 : 1
Harmonic distortion	Less than 5%
Maximum configurable power in VA	3000 VA
Max Configurable Power (Watts)	2700 W
Transfer Time	2-4 ms 4ms typical : 8ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	C-tick CE CSA GOST IRAM VDE
Standards	EN 50091-1 EN 50091-2 EN 60950 FCC Part 15 class A UL 1778

Environmental

Acoustic level	55 dBA
Heat dissipation	184 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Type	Lead-Acid battery
Extendable Run Time	1
Liquid Electrolyte Value	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	3...5 year(s)
Battery power in VAH	738 VAh runtime

Battery Charge Power (Watts)	245 W rated
Battery option	SMX120BP 1 2214 VAh SMX120BP 2 3690 VAh SMX120BP 3 5166 VAh SMX120BP 4 6642 VAh SMX120BP 6 9594 VAh SMX120BP 8 12546 VAh SMX120BP 10 15498 VAh

Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	1

Surge Protection and Filtering

Surge energy rating	645 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	00731304292630
Package weight(Lbs)	105.23 lb(US) (47.73 kg)

Packing Units

Package 1 Height	12.99 in (33 cm)
Package 1 width	23.07 in (58.6 cm)
Package 1 Length	24.92 in (63.3 cm)
Number of Units in Package 3	6
Package 3 Weight	856.92 lb(US) (388.69 kg)
Package 3 Height	43.50 in (110.49 cm)
Package 3 width	48.00 in (121.92 cm)
Package 3 Length	31.00 in (78.74 cm)
Pallet unit layers	2
Pallet layers	4

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional on-site warranties available, optional extended warranties available
----------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMX3000HVT](#)