# Product data sheet Characteristics

# SRT6KRMXLT-5KTF

APC Smart-UPS On-Line, 6kVA/6kW, Rackmount 6U, 208V, 12x 5-20R+2x L6-20R +2x L6-30R NEMA, Network Card+SmartSlot, W/ transformer 208V-120V, W/ rail kit







#### Overview

Lead time	Usually in Stock	
-----------	------------------	--

#### Main

Main Input Voltage	208 V
Other Input Voltage	240 V
Main Output Voltage	120 V 208 V
Other Output Voltage	240 V
Kw Rating	6000 W
Rated power in VA	6000 VA
Nb of power socket outlets	12 NEMA 5-20R 2 NEMA L6-20R 2 NEMA L6-30R
Output connector type	Hard Wire 3-wire (2PH + G) 1
Number of rack unit	6U
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack Mounting brackets Rack Mounting support rails Temperature Probe USB cable Warranty card Web/SNMP Management Card

#### General

Product web sub-family	High density
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

# Physical

Color	Black
Height	10.35 in (26.3 cm)
Width	17.01 in (43.2 cm)
Depth	28.31 in (71.9 cm)
Net Weight	230.01 lb(US) (104.33 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal

# Input

Input Frequency	40 - 70 Hz auto-sensing
Number of input connectors	1 Hard Wire 3-wire (2PH + G)
Efficiency at full load	100275 V adjustable (half load)

### Output

Max Configurable Power (Watts)	6000 W
Harmonic distortion	Less than 2%
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Crest factor	3:1
Topology	Double Conversion Online
Waveform Type	Sine wave
Bypass type	Internal Bypass (Automatic and Manual)
Maximum configurable power in VA	6000 VA

### Conformance

Product Certifications	ENERGY STAR V2.0 (USA) FCC part 15 class A UL 1778	
Standards	CSA C22.2 No.107.3-05	

### Environmental

Ambient Air Temperature for Operation	32104 °F (040 °C)
Relative Humidity	095 % non-condensing
Operating altitude	010000 ft
Ambient Air Temperature for Storage	5113 °F (-1545 °C)
Storage Relative Humidity	095 % Non-condensing
Storage altitude	050000 ft (0.0015240.00 m)
Acoustic level	55 dBA
Heat dissipation	1402 Btu/h
IP degree of protection	IP20

### Batteries & Runtime

	•	
Included Battery Modules	U	
Battery Slots Empty	0	
Typical recharge time	1.5 h	
RBC Quantity	1	
Battery Voltage	192V	
Battery Charge Power (Watts)	579 W rated	
Battery power in VAH	875 VAh runtime	
Battery Life	35 year(s)	

Battery option	SRT192RMBP 1 2625 VAh SRT192RMBP 2 4375 VAh
	SRT192RMBP 3 6125 VAh SRT192RMBP 4 7875 VAh
	SRT192RMBP 5 9625 VAh
	SRT192RMBP 6 11375 VAh SRT192RMBP 8 14875 VAh
	SRT192RMBP 10 18375 VAh
Extendable Run Time	1
Communications & Management	
Free slots	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes
Surge Protection and Filtering	
Surge energy rating	480 J
Ordering and shipping details	
Package weight(Lbs)	259.99 lb(US) (117.93 kg)
Dankin a Unita	
Packing Units Package 1 Height	24.57 in (62.4 cm)
Package 1 width	24.49 in (62.2 cm)
Package 1 Length	37.80 in (96 cm)
Number of Units in Package 3	6
<u> </u>	
Offer Sustainability	
Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant    EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	€Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available
Contractual warranty	
Morronty	2 years renair or replace (evaluding bettery) and 2 years for bettery



3 years repair or replace (excluding battery) and 2 years for battery

Warranty

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric: SRT6KRMXLT-5KTF