


# STBNIP2311

standard Network Interface Module STB -  
Ethernet modbus TCP/IP - 10...100 Mbits



## Main

Range of Product	Modicon STB distributed I/O solution
Product or Component Type	Standard Network Interface Module
Integrated connection type	Ethernet Modbus TCP/IP IEEE 802.3 2 female RJ45 double shielded twisted pair via Ethernet network) Ethernet Modbus TCP/IP IEEE 802.3 HE-13 RS232 port) Ethernet Modbus TCP/IP IEEE 802.3 8-way female RS232 port)
Port Ethernet	10BASE-T/100BASE-T
Exchange mode	Half or full duplex
Number of segments	1 primary, maximum 6 extensions
Transmission rate	10/100 Mbit/s 0.00...328.08 ft (0...100 m) per segment
Structure type	Industrial LAN Ethernet Modbus TCP/IP network

## Complementary

Number of addressable I/O module	0...32 per island
Communication Service	SNMP agent BootP/DHCP protocol Modbus TCP/IP messaging Embedded web (configuration,diagnostics and access to variable)
[Us] rated supply voltage	24 V DC
Power supply type	SELV
Maximum supply current	700 A
Supply voltage limits	19.2...30 V
Input current	550 mA supply circuit
Nominal output current	0.575 A 140...158 °F (60...70 °C) 1.2 A
Output voltage	5.25 V DC +/- 0.21 %)logic bus
Marking	CE
Overvoltage category	II
Status LED	1 LED ACT 1 LED island state (RUN) 1 LED module error (ERR) 1 LED MS 1 LED NS 1 LED power supply (PWR) 1 LED test mode (TEST)
Depth	2.76 in (70 mm)
Height	1.59 in (40.5 mm)
Width	5.12 in (130 mm)
Net Weight	0.32 lb(US) (0.145 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	IEC 61131-2 : 2003 FM Class 1 division 2, groups A, B, C and D T4A with 70 °C
Product Certifications	UL ODVA C-tick ATEX Cat 3G CSA
Pollution degree	2 IEC 60664-1
Operating altitude	<= 6561.68 ft (2000 m)
IP degree of protection	IP20 conforming to EN 61131-2 class 1
Ambient air temperature for operation	32...140 °F (0...60 °C) without derating) -13...158 °F (-25...70 °C) with derating factor)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Relative humidity	95 % 140 °F (60 °C) without condensation
Vibration resistance	3 gn 58...150 Hz 35 x 7.5 mm symmetrical DIN rail 5 gn 58...150 Hz 35 x 15 mm symmetrical DIN rail +/-0.35 mm 10...58 Hz
Shock resistance	30 gn 11 ms IEC 88 reference 2-27

## Ordering and shipping details

Category	18215-ADVANTYS STB I/O
Discount Schedule	PC32
GTIN	3595864062273
Nbr. of units in pkg.	1
Package weight(Lbs)	6.35 oz (180.0 g)
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.65 in (4.2 cm)
Package 1 width	2.76 in (7 cm)
Package 1 Length	5.12 in (13 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	30
Package 2 Weight	12.35 lb(US) (5.6 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)


## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[STBNIP2311](#)