



### Overview

Presentation	Intelligent and efficient power protection enabling multi-regional deployment.
Lead time	Usually Ships within 4 Weeks

### Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Kw Rating	500 W
Rated power in VA	750 VA
Plug standard	IEC 320 C14
Nb of power socket outlets	6 IEC 320 C13 2 IEC Jumpers
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable User Manual

### General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Variant option	Factory Set Voltage

### Physical

Color	Black
Height	6.18 in (15.7 cm)
Width	5.39 in (13.7 cm)
Depth	14.09 in (35.8 cm)
Net Weight	29.06 lb(US) (13.18 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	No

### Input

Efficiency at full load	151...302 V adjustable 160...285 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Harmonic distortion	Less than 5 % at full load
Maximum configurable power in VA	750 VA
Max Configurable Power (Watts)	500 W
Transfer Time	4ms typical : 8ms maximum
Topology	Line Interactive
Waveform Type	Sine wave

## Conformance

Product Certifications	CE
Standards	UL 1778

## Environmental

Acoustic level	55 dBA
Heat dissipation	90 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

## Batteries & Runtime

Additional information	Configurable for 220 or 230V nominal output voltage
Battery Voltage	24 V
Extendable Run Time	0
Battery Capacity	7.0 Ah
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Life	3...5 year(s)
Battery power in VAh	149 VAh runtime
Battery Charge Power (Watts)	50 W rated

## Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : and Overload Indicators
Free slots	1

## Surge Protection and Filtering

Let Through Voltage Rating	400 V
Surge energy rating	340 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

## Ordering and shipping details

GTIN	731304253365
Package weight(Lbs)	32.08 lb(US) (14.55 kg)

## Packing Units

Package 1 Height	10.98 in (27.9 cm)
Package 1 width	10.75 in (27.3 cm)
Package 1 Length	19.49 in (49.5 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SUA750IX38](#)