



## Schneider Electric Relays



200 N. Martingale Rd., Suite 1000

Schaumburg, IL 60173

Phone: 847-441-2540 • Fax: 847-881-0741

E-Mail: [relays@schneider-electric.com](mailto:relays@schneider-electric.com) • Web site: [www.serelays.com](http://www.serelays.com)

ITEM # W9AS5D52-24, 9A MINIATURE POWER RELAYS / SPDT, 30 AMP RATING (DC)



[SPECIFICATIONS](#) | [CONTACT CHARACTERISTICS](#) | [COIL CHARACTERISTICS](#) | [PERFORMANCE CHARACTERISTICS](#) | [ENVIRONMENT](#) | [PRODUCT CERTIFICATIONS](#)

### Specifications

Check Inventory

[Check Distributor Inventory](#)

Status

Standard

Cover Style

Flange Cover

Figure

B

California Proposition 65 Warning



**WARNING:** This product can expose you to chemicals including:  
**Substance 1:** Nickel compounds, which is known to the State of California to cause cancer.

**Substance 2:** DIDP, which is known to the State of California to cause birth defects or other reproductive harm.

For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)

### Contact Characteristics

Contact Rating

Normally Closed Contact: 15 A  
Normally Open Contact: 30 A

Contact Configuration

SPDT

Contact Materials

Silver Alloy

<b>Maximum Switching Voltage (V)</b>	300 V
<b>Switching Current at Voltage (AC, Resistive)</b>	Normally Closed Contact: 10 A at 240 VAC 50/60 Hz Normally Open Contact: 20 A at 240 VAC 50/60 Hz
<b>Switching Current at Voltage (DC, Resistive)</b>	Normally Closed Contact: 10 A at 28 VDC Normally Open Contact: 30 A at 28 VDC
<b>Switching Current at Voltage (Pilot Duty)</b>	Normally Closed Contact: 275 VA Normally Open Contact: 470 VA
<b>Minimum Switching Requirement</b>	1 A at 5 VDC, 12 VAC

Coil Characteristics		—
<b>Nominal Input Voltage</b>	24 VDC	
<b>Coil Resistance (Ohms)</b>	576 Ohm	
<b>Operating Range - % of Nominal (AC)</b>	80 to 110 %	
<b>Operating Range - % of Nominal (DC)</b>	75 to 110 %	
<b>Average Consumption (AC / VA)</b>	2.80 VA	
<b>Average Consumption (DC / W)</b>	1 W	
<b>Drop-out Voltage Threshold (DC)</b>	10 %	
<b>Drop-out Voltage Threshold (AC)</b>	10 %	

Performance Characteristics		—
<b>Electrical Life (UL508), Operations at Rated Current (Resistive)</b>	100000	
<b>Mechanical Life, Unpowered</b>	10000000	
<b>Operating Time (Response Time)</b>	15 ms	
<b>Dielectric Strength - Between Coil and Contact</b>	2500 VAC (rms)	
<b>Dielectric Strength - Between Poles</b>	1500 VAC (rms)	

Environment		—
<b>Ambient Air Temperature around the Device - Storage</b>	-40 to +85 °C	
<b>Ambient Air Temperature around the Device - Operation</b>	-40 to +55 °C	

Shock Resistance		10 g-n
Product Certifications		—
Agency Approvals		UL RoHs

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9AS5D52-24](#) [9AS7D24](#)