



Main

Range	TeSys
Device short name	MN
Product or Component Type	Voltage release
Device application	Control
Range compatibility	TeSys GV4 TeSys BV4
Voltage release type	Undervoltage release
[Uc] control circuit voltage	24 V AC 50/60 Hz 24 V DC

Complementary

[Ui] rated insulation voltage	24 V IEC 60947-1
Threshold tripping voltage	< 0.35 Un failsafe opening 0.35...0.7 Un possible opening 0.85...1.1 Un enabled closing
Mounting Mode	Internal mounting
Maximum inrush power in VA	7 VA
Maximum inrush power in W	2 W
Maximum hold-in power consumption in VA	7 VA
Maximum hold-in power consumption in W	2 W
Mechanical durability	20000 cycles
Operating time	< 50 ms
Connections - terminals	Spring terminals 1 0.00...0.00 in ² (0.5...1.5 mm ²) flexible without cable end
Wire stripping length	0.31 in (8 mm)

Environment

Quantity per Set	Set of 1
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV4AU027](#)