

Product data sheet

Characteristics

SGA8179L05

MAGNET SWITCH 480 V dc - 1.0 Amp - 25 VA
- Cable l = 5 m

Product availability: Stock - Normally stocked in distribution facility



Main

Product or component type	Coded magnetic system
Contacts type and composition	1 NO
Material	Plastic
Electrical connection	Pre-cabled
Cable length	16.4 ft (5 m)
System Voltage	480 V DC

Complementary

Protection type	Overload and short-circuit protection
Breaking capacity	25 VA

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

Ordering and shipping details

Category	22487 - SENSORS, PROXIMITY, U S
Discount Schedule	DS2
GTIN	00785901092001
Nbr. of units in pkg.	1
Package weight(Lbs)	1.51
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SGA8179L05](#)