

# Product data sheet

## Characteristics

### SGA8182L10

MAGNET SWITCH - 10 VA max - 200 V dc /  
500 mA max cable l = 10 m

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product or component type	Coded magnetic system
---------------------------	-----------------------

Contacts type and composition	1 NO
-------------------------------	------

Material	Plastic
----------	---------

Electrical connection	Pre-cabled
-----------------------	------------

Cable length	32.81 ft (10 m)
--------------	-----------------

System Voltage	200 V DC
----------------	----------

#### Complementary

Protection type	Overload and short-circuit protection
Breaking capacity	10 VA

#### Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)

#### Ordering and shipping details

Category	22487 - SENSORS, PROXIMITY, U S
Discount Schedule	DS2
GTIN	00785901092018
Nbr. of units in pkg.	1
Package weight(Lbs)	0.280000000000000003
Returnability	N
Country of origin	US

#### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

#### Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SGA8182L10](#)