


Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Device short name	GV3A
Product or component type	Auxiliary contact block
Product compatibility	GV3ME
Mounting location	Front side
Auxiliary contacts operation	Fault signal 1 NO
Pole contact composition	1 NO
Connections - terminals	Screw clamp terminals 1 cable 0...0 in ² (0.75...2.5 mm ²) - cable stiffness: flexible - without cable end Screw clamp terminals 2 cable 0...0 in ² (0.75...2.5 mm ²) - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable 0...0 in ² (0.75...2.5 mm ²) - cable stiffness: flexible - with cable end Screw clamp terminals 2 cable 0...0 in ² (0.75...1.5 mm ²) - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: solid Screw clamp terminals 2 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: solid
Quantity per set	Set of 10

Complementary

[Ui] rated insulation voltage	600 V - conforming to UL 508 690 V - conforming to IEC 60947-1 600 V - conforming to CSA C22.2 No 14
System Voltage	48...690 V AC 24...220 V DC
[Ith] conventional free air thermal current	6 A
Protection type	GB2CB... circuit breaker rating according to operational current for Ue ≤ 415 V GG fuse ≤ 6 A
Mechanical durability	1000 cycles
Rated operational power in VA	240 VA at 48 V AC-11 - electrical durability: 1000 cycles 450 VA at 440 V AC-11 - electrical durability: 1000 cycles 450 VA at 500 V AC-11 - electrical durability: 1000 cycles 200 VA at 690 V AC-11 - electrical durability: 1000 cycles 460 VA at 110...127 V AC-11 - electrical durability: 1000 cycles 800 VA at 220...240 V AC-11 - electrical durability: 1000 cycles 850 VA at 380...415 V AC-11 - electrical durability: 1000 cycles
Rated operational power in W	180 W at 24 V DC-11 - electrical durability: 1000 cycles 180 W at 48 V DC-11 - electrical durability: 1000 cycles 135 W at 60 V DC-11 - electrical durability: 1000 cycles 105 W at 110 V DC-11 - electrical durability: 1000 cycles 90 W at 220 V DC-11 - electrical durability: 1000 cycles
Width	0.35 in (9 mm)

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. It is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22366 - MAN STR PROTECTORS-GV1/GV3
Discount Schedule	I11
GTIN	00785901444848
Nbr. of units in pkg.	1
Package weight(Lbs)	5.0000000000000003E-2
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0723 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details- Go to CaP for more details
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV3A09](#)